


4.2 MCW profile wiper seals, inch sizes

d 0.5 – 2.125 in.




4.2

Dimensions					Designation
d ¹⁾	D ±0.001	L +0.015	S	C min.	
in.					-
0.5	1	0.25	0.25	0.312	MCW-500-H9B
0.625	1.125	0.312	0.25	0.312	MCW-625-H9B
0.75	1.25	0.312	0.25	0.312	MCW-750-H9B
0.875	1.375	0.312	0.25	0.312	MCW-875-H9B
1	1.5	0.312	0.25	0.312	MCW-1000-H9B
1.125	1.625	0.312	0.25	0.312	MCW-1125-H9B
1.187	1.623	0.218	0.25	0.312	MCW218-1187-250-H9B
1.25	1.75	0.312	0.25	0.312	MCW-1250-H9B
1.375	1.875	0.312	0.25	0.312	MCW-1375-H9B
1.5	2	0.312	0.25	0.312	MCW-1500-H9B
	2.125	0.312	0.312	0.312	MCW312-1500-312-H9B
1.562	1.875	0.156	0.375	0.312	MCW156-1562-375-H9B
1.625	2.125	0.312	0.25	0.312	MCW-1625-H9B
1.75	2.25	0.312	0.25	0.312	MCW-1750-H9B
	2.5	0.375	0.375	0.312	MCW375-1750-375-H9B
1.875	2.375	0.312	0.25	0.312	MCW-1875-H9B
2	2.5	0.312	0.25	0.312	MCW-2000-H9B
	2.75	0.375	0.375	0.312	MCW375-2000-375-H9B
	2.875	0.438	0.25	0.312	MCW438-2000-250-H9B
2.125	2.625	0.312	0.25	0.312	MCW-2125-H9B
	2.875	0.375	0.375	0.312	MCW375-2125-375-H9B

¹⁾ Tolerance is determined by the rod seal

4.2 MCW profile wiper seals, inch sizes

d 2.25 – 8.5 in.



Dimensions					Designation
d ¹⁾	D ±0.001	L +0.015	S	C min.	
in.					-
2.25	2.75 3	0.312 0.375	0.25 0.25	0.312 0.312	MCW-2250-H9B MCW375-2250-250-H9B
2.375	2.875	0.312	0.25	0.312	MCW-2375-H9B
2.5	3 3.19	0.312 0.345	0.25 0.375	0.312 0.312	MCW-2500-H9B MCW345-2500-375-H9B
2.625	3.125 3.375	0.312 0.375	0.25 0.375	0.312 0.312	MCW-2625-H9B MCW375-2625-375-H9B
2.75	3.25 3.5	0.312 0.375	0.25 0.375	0.312 0.312	MCW-2750-H9B MCW375-2750-375-H9B
3	3.5 3.75	0.312 0.375	0.25 0.375	0.312 0.312	MCW-3000-H9B MCW375-3000-375-H9B
3.125	3.75	0.312	0.312	0.312	MCW-3125-H9B
3.25	3.875	0.312	0.312	0.312	MCW-3250-H9B
3.5	4.125 4.25	0.312 0.375	0.312 0.312	0.312 0.312	MCW-3500-H9B MCW375-3500-312-H9B
3.625	4.25	0.312	0.312	0.312	MCW-3625-H9B
3.75	4.375	0.312	0.312	0.312	MCW-3750-H9B
4	4.625	0.312	0.312	0.312	MCW-4000-H9B
4.25	4.875	0.312	0.312	0.312	MCW-4250-H9B
4.5	5.125	0.312	0.312	0.312	MCW-4500-H9B
5	5.625	0.312	0.312	0.312	MCW-5000-H9B

¹⁾ Tolerance is determined by the rod seal

Dimensions					Designation
d ¹⁾	D ±0.001	L +0.015	S	C min.	
in.					-
5.5	6.125 6.25	0.375 0.375	0.312 0.312	0.312 0.312	MCW-5500-H9B MCW375-5500-312-H9B
5.75	6.375 6.75	0.375 0.5	0.312 0.5	0.312 0.375	MCW-5750-H9B MCW500-5750-500-H9B
6	6.625	0.375	0.312	0.312	MCW-6000-H9B
6.5	7.125	0.312	0.312	0.312	MCW312-6500-312-H9B
6.75	7.375 7.375	0.312 0.375	0.312 0.312	0.312 0.312	MCW312-6750-312-H9B MCW-6750-H9B
7	7.75	0.375	0.312	0.312	MCW375-7000-312-H9B
8	8.75	0.375	0.375	0.312	MCW375-8000-375-H9B
8.5	9.125	0.375	0.312	0.312	MCW-8500-H9B

Other sizes are available on request

¹⁾ Tolerance is determined by the rod seal