



Safety data sheet

Issue date: 26-05-2015

Version: 01.00/GBR

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Trade name: LGLS 0

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended uses: Lubricant Lubricating grease

1.3. Details of the supplier of the safety data sheet

Supplier: SKF MAINTENANCE PRODUCTS
Postbus 1008
NL-3430 BA Nieuwegein
The Netherlands
Tel: +31 30 6307200
Email: sebastien.david@skf.com
WWW: www.skf.com

1.4. Emergency telephone number

0870 600 6266 (UK only) Only available to health professionals.

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

DPD-classification (Directive 1999/45/EC):

CLP-classification (Regulation (EC) No 1272/2008):

The product shall not be classified as hazardous according to the classification and labelling rules for substances and mixtures.

Most serious harmful effects:

May cause slight irritation to the skin and eyes.

2.2. Label elements

The product shall not be classified as hazardous according to the classification and labelling rules for substances and mixtures.

Supplemental information:

Safety data sheet available on request.

2.3. Other hazards

Assessment to determine PBT and vPvB has not been made.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Registration number	CAS/EC Number	Substance	DSD-classification (Directive 67/548/EEC)/ CLP-classification (Regulation (EC) No 1272/2008)	w/w%	Note
.	85940-28-9	Phosphorodithioic acid, mixed	Xi;R36/38 N;R51/53	<2,5	.

288-917-4 O,O-bis(2-ethylhexyl and iso-Bu and iso-Pr) esters, zinc salts Skin Irrit. 2;H315 Eye Irrit. 2;H319 Aquatic Chronic 2;H411

Please see section 16 for the full text of R-phrases and H-phrases.

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation: Seek fresh air. Seek medical advice in case of persistent discomfort.

Ingestion: Wash out mouth thoroughly and drink 1-2 glasses of water in small sips. Seek medical advice in case of persistent discomfort.

Skin: Remove contaminated clothing. Wash skin with soap and water. Seek medical advice in case of persistent discomfort.

Eyes: Flush with water (preferably using eye wash equipment) until irritation subsides. Seek medical advice if symptoms persist.

Other information: When obtaining medical advice, show the safety data sheet or label.

4.2. Most important symptoms and effects, both acute and delayed

May cause slight irritation to the skin and eyes.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptoms. No special immediate treatment required.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media Extinguish with powder, foam, carbon dioxide or water mist. Use water or water mist to cool non-ignited stock.

Unsuitable extinguishing media Do not use water stream, as it may spread the fire.

5.2. Special hazards arising from the substance or mixture

Not flammable, but combustible. Product decomposes in fire conditions or when heated to high temperatures, and inflammable and toxic gases may be released.

5.3. Advice for firefighters

Wear Self-Contained Breathing Apparatus (SCBA) with chemical resistant gloves. Move containers from danger area if it can be done without risk. Avoid inhalation of vapour and flue gases – seek fresh air.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel: Stay upwind/keep distance from source. Stop leak if this can be done without risk. Wear gloves. Wear safety goggles if there is a risk of eye splash.

For emergency responders: In addition to the above: Normal protective clothing equivalent to EN 469 is recommended.

6.2. Environmental precautions

Prevent spillage from entering drains and/or surface water.

6.3. Methods and material for containment and cleaning up

Contain and absorb spill with sand or other absorbent material and transfer to suitable waste containers. Wipe up minor spills with a cloth.

6.4. Reference to other sections

See section 8 for type of protective equipment. See section 13 for instructions on disposal.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Running water and eye wash equipment should be available. Wash hands before breaks, before using restroom facilities, and at the end of work.

7.2. Conditions for safe storage, including any incompatibilities

The product should be stored safely, out of reach of children and away from food, animal feeding stuffs, medicines, etc. Do not store with the following: Strong oxidisers. Store at temperatures below 45 °C.

7.3. Specific end use(s)

None.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Legal basis: EH40/2005 Workplace exposure limits. Last amended December 2011.

Contains no substances subject to reporting requirements.

8.2. Exposure controls

Appropriate engineering controls: Wear the personal protective equipment specified below.

Personal protective equipment, eye/face protection: Wear safety goggles if there is a risk of eye splash. Eye protection must conform to EN 166.

Personal protective equipment, skin protection: Plastic or rubber gloves recommended.

Personal protective equipment, respiratory protection: Not required.

Environmental exposure controls: Ensure compliance with local regulations for emissions.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Paste / Fat.

Colour: Red

Odour: No data

Odour threshold: No data

pH (solution for use): No data

pH (concentrate): No data

Melting point/freezing point: No data

Initial boiling point and boiling range: No data

Flash point: > 150 °C

Evaporation rate: No data

Flammability (solid, gas): No data

Upper/lower flammability limits: No data

Upper/lower explosive limits: No data

Vapour pressure: No data

Vapour density: No data

Relative density: No data

Solubility: No data

Partition coefficient n-octanol/water: No data

Auto-ignition temperature: No data

Decomposition temperature: No data

Viscosity: No data

Explosive properties: No data

Oxidising properties: No data

9.2. Other information

< 1000 kg/m³ (25 °C)

SECTION 10: Stability and reactivity

10.1. Reactivity

	Reacts with the following: Strong oxidisers.
10.2. Chemical stability	The product is stable when used in accordance with the supplier's directions.
10.3. Possibility of hazardous reactions	None known.
10.4. Conditions to avoid	Avoid temperatures > 45 °C.
10.5. Incompatible materials	Strong oxidisers.
10.6. Hazardous decomposition products	Product decomposes in fire conditions or when heated to high temperatures, and inflammable and toxic gases may be released.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity - oral:	The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met. Ingestion may cause discomfort. LGLS 0: LD50 = 5754 mg/kg 85940-28-9: Rat: LD50 = 3000 mg/kg
Acute toxicity - dermal:	The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met. LGLS 0: LD50 = 3569 mg/kg
Acute toxicity - inhalation:	The product does not have to be classified. Test data are not available.
Skin corrosion/irritation:	The product does not have to be classified. Test data are not available. May cause slight irritation.
Serious eye damage/eye irritation:	The product does not have to be classified. Test data are not available. May cause eye irritation.
Respiratory sensitisation or skin sensitisation:	The product does not have to be classified. Test data are not available.
Germ cell mutagenicity:	The product does not have to be classified. Test data are not available.
Carcinogenic properties:	The product does not have to be classified. Test data are not available.
Reproductive toxicity:	The product does not have to be classified. Test data are not available.
Single STOT exposure:	The product does not have to be classified. Test data are not available.
Repeated STOT exposure:	The product does not have to be classified. Test data are not available.
Aspiration hazard:	The product does not have to be classified. Test data are not available.
Other toxicological effects:	None known.

SECTION 12: Ecological information

12.1. Toxicity

The product does not have to be classified. Based on existing data, the classification criteria

are deemed not to have been met. The product contains small quantities of environmentally hazardous substances. Occasional major emissions or frequently recurring minor emissions may have a harmful or disturbing effect.

Acute toxicity: 85940-28-9:
Fish:
Cyprinodon variegatus 96hLC50 = 2,2 mg/l

12.2. Persistence and degradability

Not expected to be biodegradable.

12.3. Bioaccumulative potential

No bioaccumulation expected.

12.4. Mobility in soil

Not expected to be mobile in soil.

12.5. Results of PBT and vPvB assessment

No assessment has been made.

12.6. Other adverse effects

German water pollution classification (WGK): 1

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Contact the local authorities. Avoid discharge to drain or surface water.

EWC code: Depends on line of business and use, for instance 12 01 12*spent waxes and fats

Absorbent/cloth contaminated with the product:

EWC code: 15 02 03 Absorbents, filter materials, wiping cloths and protective clothing other than those mentioned in 15 02 02.

Uncleansed packaging is to be disposed of via the local waste-removal scheme. Empty, cleansed packaging should be disposed of for recycling.

SECTION 14: Transport information

The product is not covered by the rules for transport of dangerous goods.

14.1. UN number -

14.2. UN proper shipping name -

14.3. Transport hazard class(es) -

14.4. Packing group -

14.5. Environmental hazards -

14.6. Special precautions for user -

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code -

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Special provisions: None.

15.2. Chemical safety assessment

Chemical safety assessment has not been performed.

SECTION 16: Other information

Changes have been made in the following sections: 1 - 16.

Abbreviation explanations:

PBT: Persistent, Bioaccumulative and Toxic
vPvB: Very Persistent and Very Bioaccumulative
STOT: Specific Target Organ Toxicity

Classification method:

Calculation based on the hazards of the known components.

R-phrases:

R36/38 Irritating to eyes and skin.
R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

H-phrases:

H315 Causes skin irritation.
H319 Causes serious eye irritation.
H411 Toxic to aquatic life with long lasting effects.

Training:

A thorough knowledge of this safety data sheet should be a prerequisite condition.

Other information:

This safety data sheet has been prepared for and applies to this product only. It is based on our current knowledge and the information that the supplier was able to provide about the product at the time of preparation. The safety data sheet complies with applicable law on preparation of safety data sheets in accordance with 1907/2006/EC (REACH) as subsequently changed.
