

Sealless immersion pumps for machine tools and filter systems

Do you overhaul machine tools
and filter systems? Do you work with
immersion pumps?

We offer immersion pumps with:

- Delivery rates up to
 $Q_{\max} = 1250 \text{ l/min}$
- Delivery pressures up to
 $P_{\max} = 120 \text{ bar}$
- Temperature ranges
 -30°C to $+80^{\circ}\text{C}$



The company

Spandau Pumps has been developing and manufacturing centrifugal and screw pumps for over 80 years. These high-quality pumps are used worldwide and are preferred by major manufacturers of machine tools and filter systems.

We are your pump specialist and help you with pump design!

- Extensive range of products
- Expert consulting
- Short delivery times

We offer screw pumps and centrifugal pumps for new and replacement equipment in:

- Repair, overhaul, and maintenance
- Machine refurbishing
- Retrofitting

We offer a large range of pumps:

- Delivery rates up to 1250 l/min
- Delivery pressures up to 120 bar
- Flexible immersion depths up to 2000 mm
- Easy installation and commissioning

Large range of designs

From standard solutions to special customer-specific solutions, we supply centrifugal and screw pumps with delivery pressures up to 120 bar. The easy-to-use immersion pumps are installed directly in the coolant reservoir and are available in numerous designs for various pumped media, delivery rates, and delivery heads. They can be provided with various drive options, from standard motors according to DIN EN 60034 through to protection class EExd. Furthermore, the immersion pumps can be supplied with all standard electrical connection ratings used around the world.

SKF Lubrication Systems Germany GmbH
Product Range Spandau Pumps
Motzener Strasse 35/37 · 12277 Berlin · Germany
PO Box 970444 · 12704 Berlin · Germany
Tel. +49 (0)30 72002-0 · Fax +49 (0)30 72002-261
kontakt@spandaupumpen.de
www.spandaupumpen.de

This brochure was presented to you by: