

300 and 400 MPa (43 500 and 58 000 psi)

SKF Oil Injector 226400 E series

The 226400 E series is suitable for many applications using the SKF Oil Injection Method. The injector is supplied with an oil reservoir in a compact carrying case. The injector can be mounted directly onto the work piece or connected to an adapter block to make a floor standing model, making it easy to connect pressure gauges and high-pressure pipes. For applications where 400 MPa (58 000 psi) is required, the SKF 226400 E/400 is available.

- Easy to operate.
- Compact carrying case.
- When the pressure is released, the unused oil is automatically returned to the reservoir, minimizing the risk of oil leakage to the environment.
- Oil container capacity 200 cm³ (12.2 in.³).
- Can be used with a wide range of accessories, such as:
 - Adapter block
 - Pressure gauges
 - High pressure pipes
 - Connecting nipples

Typical applications

- Bearings
- Couplings
- Railway wheels
- Gear wheels
- Flywheels
- SKF OK Couplings
- For many oil injection applications where maximum pressures of up to 400 MPa (58 000 psi) is required



Technical data

Designation	226400 E	226400 E/400
Maximum pressure	300 MPa (43 500 psi)	400 MPa (58 000 psi)
Volume per stroke	0,23 cm ³ (0.014 in ³)	0,23 cm ³ (0.014 in ³)
Oil reservoir capacity	200 cm ³ (12.2 in ³)	200 cm ³ (12.2 in ³)
Connecting threads	G ^{3/4}	G ^{3/4}
Weight	2,2 kg (4.8 lb)	2,2 kg (4.8 lb)



226400 E series used with adapter block, pressure gauge and high pressure pipe.

© SKF is a registered trademark of the SKF Group.

© SKF Group 2014

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

PUB MP/P8 14845 EN · September 2014

