

SKF Gloves

Personal protective equipment

SKF Heat Resistant Gloves TMBA G11

The SKF TMBA G11 are specially designed for the handling of heated bearings.

- Lint free.
- Heat resistant up to 150 °C (302 °F).
- Cut resistant.
- Tested and certified for mechanical risks (EN 388) and thermal risks (EN 407).



Technical data

Designation	TMBA G11
Material	Hytex
Inner lining	Cotton
Size	9
Colour	White
Maximum temperature	150 °C (302 °F)
Pack size	1 pair

SKF Extreme Temperature Gloves TMBA G11ET

The SKF TMBA G11ET are especially designed for the safe handling of heated bearings or other components for prolonged periods.

- Withstands extreme temperatures of up to 500 °C (932 °F) unless in the presence of hot liquid or steam.
- Allows the safe handling of heated components.
- High-degree of non-flammability reduces the risk of burning.
- Extremely tough Kevlar gloves with high cut, abrasion, puncture and tear resistance for increased safety.
- Lint free.
- Tested and certified for mechanical risks (EN 388) and thermal risks (EN 407).



Technical data

Designation	TMBA G11ET
Material	Kevlar
Inner lining	Cotton
Size	10 (EN 420 size)
Colour	Yellow
Maximum temperature	500 °C (932 °F)
Pack size	1 pair

SKF Heat and Oil Resistant Gloves TMBA G11H

The SKF TMBA G11H are specially designed for the handling of hot and oily bearings.

- Offers a high degree of heat, cut, oil and water resistance.
- Melt and burn resistant.
- Maximum temperature: 250 °C (482 °F).
- Cut resistant.
- Lint free.
- Suitable for submerging in liquids with a temperature up to 120 °C (248 °F) (e.g. hot oil bath).
- Remains heat resistant when wet.
- Tested and certified for mechanical risks (EN 388) and thermal risks (EN 407).



Technical data

Designation	TMBA G11H
Material	Polyaramid
Inner lining	Nitrile
Size	10
Colour	Yellow
Maximum temperature	250 °C (482 °F)
Pack size	1 pair

SKF Disposable Grease Resistant Gloves TMBA G11D

SKF TMBA G11D gloves are specially designed to protect skin when working with lubricants. The gloves are packed in a handy box containing 25 pairs.

- Non-powdered nitrile rubber gloves
- Tight fitting for precision wear
- Excellent resistance against lubricants
- Non-allergenic



Technical data

Designation	TMBA G11D
Material	Non powdered nitrile
Size	9
Colour	blue
Pack size	25 pairs

[skf.com](https://www.skf.com) | [skf.com/mapro](https://www.skf.com/mapro) | [skf.com/lubrication](https://www.skf.com/lubrication)

© SKF is a registered trademark of the SKF Group.

© SKF Group 2020
The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

PUB MP/P8 14368/2 EN · April 2020