


SKF Ecotex

Fabric-reinforced thermoset wear strip + lubricants

Property	Unit	Value	Standard
Standard color	–	Orange	
Density	g/cm ³	1,21	–
Tensile strength	MPa	55	–
Hardness	Shore D	67–77	–
Compressive strength normal to laminate	MPa	413 (unbroken)	–
parallel to laminate	MPa	165 (unbroken)	–
Moisture absorption	%	< 0,1	–
Coefficient of friction (dry)	–	0,13–0,15	–
Minimum service temperature	°C	–40	–
Maximum service temperature	°C	+120	–
in water	°C	+100	–

IMPORTANT NOTE: The values shown above are only valid for material samples prepared for test purposes according to the stated standards.

© SKF is a registered trademark of the SKF Group.

© SKF Group 2014

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

PUB SE/P8 12485/1 EN · October 2014

