

Cross reference guide – Ball bearing units

Pillow block units (P2B, P2BL, P2BM Series)



Housing material/duty	Locking method	Seal type	Baldor•Dodge	Fafnir	Sealmaster	Rexnord / Link-Belt	Browning	AMI	SKF
Cast iron, standard duty	Set screw	Seal	P2B-VSC-___	SAS ___	NP-__ C	P3S ___ E	VPS-1__	BP ___	P2B ___ RM
		Seal	P2B-VSCB-___	SAK ___	NPL-__ C	PL3S ___ E	VPLS-1__	BLP ___	P2BL ___ RM
		Seal & flinger	P2B-SC-___	YAS ___ SGT	NP-__	P3U ___ N	VPS-2__	UCP ___	P2B ___ TF
		Seal & flinger	P2B-SCB-___	YAK ___ SGT	NPL-__	PL3U ___ N	VPLS-2__	UCLP ___	P2BL ___ TF
		Seal & flinger, AH	P2B-SCAH-___	-	NP-__ CXU	-	VPS-2__ AH	UCP ___ AM	P2B ___ TF -AH
		Seal & flinger, AH	P2B-SCBAH-___	-	NPL-__ CXU	-	VPLS-2__ AH	UCLP ___ AM	P2BL ___ TF -AH
	Eccentric	Seal	P2B-SXV-___	VAS ___	-	P3W ___ E	VPE-1__	KHP ___	P2B ___ FM
		Seal	P2B-SXVB-___	VAK ___	-	PL3W ___ E	VPLE-1__	KHLP ___	P2BL ___ FM
		Seal & flinger	P2B-SXR-___	RAS ___	-	P3Y ___ N	VPE-2__	UGP ___	P2B ___ WF
		Seal & flinger, AH	P2B-SXRAH-___	-	-	-	VPE-2__ AH	UGP ___ AM	P2B ___ WF -AH
		Seal & flinger	P2B-SXRB-___	RAK ___	-	PL3Y ___ N	VPLE-2__	UGAK ___	P2BL ___ WF
		Seal & flinger, AH	P2B-SXRBAH-___	-	-	-	VPLE-2__ AH	UGAK ___ AM	P2BL ___ WF -AH
Concentric	Seal & flinger, AH	P2B-DLAH-___	RASC-___	NP-__ T	P3CL ___ N	VPB-2__ AH	UEP ___ AM	P2B ___ LF -AH	
	Cast iron, medium duty	Set screw	P2B-SCM-___	YASM-___	MP-__	-	VPS-3__	UCPX ___	P2BM ___ TF
Concentric	Seal & flinger, AH	P2B-DLMAH-___	-	MP-__ T	-	VPB-3__ AH	UEPX ___ AM	P2BM ___ LF -AH	

Square flange – four-bolt units (SKF F4B, F4BM Series)



Housing material/duty	Locking method	Seal type	Baldor•Dodge	Fafnir	Sealmaster	Rexnord / Link-Belt	Browning	AMI	SKF
Cast iron, standard duty	Set screw	Seal	F4B-VSC-___	SCJ ___	SF-__ C	F3S ___ E	VF4S 1__	BF ___	F4B ___ RM
		Seal & flinger	F4B-SC-___	YCJ ___ SGT	SF-__	F3U ___ N	VF4S 2__	UCF ___	F4B ___ TF
		Seal & flinger	F4B-SCM-___	YCM ___	MSF-__	-	VF4S-3__	UCFX ___	F4BM ___ TF
		Seal & flinger, AH	F4B-SCAH-___	-	SF-__ CXU	-	VF4S-2__ AH	UCF ___ AM	F4B ___ TF -AH
		Seal & flinger, AH	F4B-SCMAH-___	-	MSF-__ CXU	-	VF4S-3__ AH	UCFX ___ AM	F4BM ___ TF -AH
		Eccentric	Seal	F4B-SXV-___	VCJ ___	-	F3W ___ E	VF4E 1__	KHF ___
Seal & flinger	F4B-SXR-___		RCJ ___	-	F3Y ___ N	VF4E 2__	UGSLF ___	F4B ___ WF	
Concentric	Seal & flinger, AH	F4B-DLAH-___	RCJC ___	SF-__ T	F3CL ___ N	VF4B-2__ AH	UEF ___ AM	F4B ___ LF -AH	
	Cast iron, medium duty	Concentric	F4B-DLMAH-___	-	MSF-__ T	-	VF4B-3__ AH	UEFX ___ AM	F4BM ___ LF -AH

Oval flange – two-bolt units (SKF F2B, F2BM Series)




Housing material/duty	Locking method	Seal type	Baldor•Dodge	Fafnir	Sealmaster	Rexnord / Link-Belt	Browning	AMI	SKF	
Cast iron, standard duty	Set screw	Seal	F2B-VSC-___	SCJT ___	SFT-__ C	FX3S ___ E	VF2S 1__	BFT ___	F2B ___ RM	
		Seal & flinger	F2B-SC-___	YCJT ___ SGT	SFT-__	FX3U ___ N	VF2S 2__	UCFT ___	F2B ___ TF	
		Seal & flinger	F2B-SCM-___	YCJTM ___	MSFT-__	-	VF2S 3__	UCFLX ___	F2BM ___ TF	
		Seal & flinger, AH	F2B-SCAH-___	-	SFT-__ CXU	-	VF2S 2__ AH	UCFT ___ AM	F2B ___ TF -AH	
		Eccentric	Seal	F2B-SXV-___	VCJT ___	-	FX3W ___ E	VF2E 1__	KHFT ___	F2B ___ FM
			Seal & flinger	F2B-SXR-___	RCJT ___	-	FX3Y ___ N	VF2E 2__	UGFJT ___	F2B ___ WF
Concentric	Seal & flinger, AH	F2B-DLAH-___	RCJTC ___	SFT-__ T	FX3CL ___ N	VF2B-2__ AH	UEFT ___ AM	F2B ___ LF -AH		

Take-up units (SKF WSTU Series)



Housing material/duty	Locking method	Seal type	Baldor•Dodge	Fafnir	Sealmaster	Rexnord / Link-Belt	Browning	AMI	SKF	
Cast iron, standard duty	Set screw	Seal	WSTU-VSC-___	-	ST-__ C	TH3S ___ E	VTWS-1__	-	WSTU ___ RM	
		Seal & flinger	WSTU-SC-___	YTU ___ SGT	ST-__	TH3U ___ N	VTWS-2__	UCST ___	WSTU ___ TF	
		Eccentric	Seal	WSTU-SXV-___	VTU ___	-	TH3W ___ E	VTWE-1__	-	WSTU ___ FM
			Seal & flinger	WSTU-SXR-___	RTU ___	-	TH3Y ___ N	VTWE-2__	-	WSTU ___ WF
		Concentric	Seal & flinger, AH	WSTU-DLAH-___	-	ST-__ T	TH3CL ___ N	VTWB-2__ AH	UEST ___ AM	WSTU ___ LF -AH

Tapped base units (SKF P2BT Series)



Housing material/duty	Locking method	Seal type	Baldor•Dodge	Fafnir	Sealmaster	Rexnord / Link-Belt	Browning	AMI	SKF	
Cast iron, standard duty	Set screw	Seal	TB-VSC-___	STB ___	TB-__ C	PT3S ___ E	VTBS-1__	BTB ___	P2BT ___ RM	
		Seal & flinger	TB-SC-___	YTB ___	TB-__	PT3U ___ N	VTBS-2__	UCTB ___	P2BT ___ TF	
		Eccentric	Seal	TB-SXV-___	VTB ___	-	PT3W ___ E	VTBE-1__	KHTB ___	P2BT ___ FM
			Seal & flinger	TB-SXR-___	RTB ___	-	PT3Y ___ N	VTBE-2__	UGTB ___	P2BT ___ WF
		Concentric	Seal & flinger, AH	TB-DLAH-___	-	TB-__ T	PT3CL ___ N	VTBB-2__	UETB ___ AM	P2BT ___ LF -AH

KEY: Shaft size cross reference – square four bolt flange, 2 7/16" size example. SKF – F4B 207 TF

Dodge	F4B-SC 207	Sealmaster	SF 39	Browning	VF4S 239
Fafnir	YCJ 2 7/16	Rexnord	F3U 239 N	AMI	UCF 212-39