Safety Data Sheet

LGET 2

Replaces date: 26/06/2022

Revision date: 02/10/2023
Version: 2.5.0

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Trade name: LGET 2

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended uses: Lubricant.

1.3. Details of the supplier of the safety data sheet

Supplier

Company:	SKF MPT
Address:	Meidoornkade 14
Zip code:	3992 AE
City:	AE Houten
Country:	NETHERLANDS (KINGDOM OF THE)
E-mail:	support.mpt@skf.com
Phone:	+31 30 6307200
Homepage:	www.skf.com

1.4. Emergency Telephone Number

Members of the public: 111 (NHS 111 (Scotland: NHS 24)).

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

CLP-classification: The product shall not be classified as hazardous according to the classification and labeling rules for substance and mixtures.

Most serious harmful effects: May cause slight irritation to the skin and eyes.

2.2. Label elements

Supplemental information

EUH210 Safety data sheet available on request.

2.3. Other hazards

The product does not contain any PBT or vPvB substances.
Endocrine disrupting properties: None known.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Substance	CAS No./ EC No./ REACH Reg. No.	Concentration	Notes	CLP-classification
1H-Benzotriazole (1,2,3)	95-14-7 202-394-1 01-2119979079-20	1 -< 5 %		Acute Tox. 4;H302 Eye Irrit. 2;H319 Aquatic Chronic 2;H411

Please see section 16 for the full text of H- / EUH-phrases.

Ingredient comments: The mineral oils in the product contain <3% DMSO extract(IP 346).

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation: Seek fresh air. Seek medical advice in case of persistent discomfort.

Ingestion: Wash out mouth thoroughly and drink 1-2 glasses of water in small sips. Seek medical advice in case of persistent discomfort.

Skin contact: Remove contaminated clothing. Wash skin with soap and water. Seek medical advice in case of persistent discomfort.

Eye contact: Flush with water (preferably using eye wash equipment) until irritation subsides. Seek medical advice if symptoms persist.

General: When obtaining medical advice, show the safety data sheet or label.

4.2. Most important symptoms and effects, both acute and delayed

May cause slight irritation to the skin and eyes.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptoms. No special immediate treatment required.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media: Extinguish with powder, foam or water mist. Use water or water mist to cool non-ignited stock.

Unsuitable extinguishing media: Do not use water stream, as it may spread the fire.

5.2. Special hazards arising from the substance or mixture

Not flammable, but combustible. The product decomposes when combusted and the following toxic gases can be formed: Carbon monoxide and carbon dioxide/ Hydrogen fluoride.

5.3. Advice for firefighters

Move containers from danger area if it can be done without risk. Avoid inhalation of vapour and flue gases - seek fresh air. Wear Self-Contained Breathing Apparatus (SCBA) with chemical resistant gloves.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel: Stop leak if this can be done without risk. Wear safety goggles if there is a risk of eye splash. Wear gloves.

For emergency responders: In addition to the above: Normal protective clothing equivalent to EN 469 is recommended.

6.2. Environmental precautions

Prevent spillage from entering drains and/or surface water.

6.3. Methods and material for containment and cleaning up

Contain and absorb spill with sand or other absorbent material and transfer to suitable waste containers. Wipe up minor spills with a cloth.

6.4. Reference to other sections

See section 8 for type of protective equipment. See section 13 for instructions on disposal.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Use the product under well-ventilated conditions. Running water and eye wash equipment should be available. Wash hands before breaks, before using restroom facilities, and at the end of work.

7.2. Conditions for safe storage, including any incompatibilities

The product should be stored safely, out of reach of children and away from food, animal feeding stuffs, medicines, etc. Keep in tightly closed original packaging. Avoid contact with moisture and water. Do not store with the following: Alkaline metals/ Acids.

7.3. Specific end use(s)

No special uses in addition to identified uses in 1.2.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational exposure limit: Contains no substances subject to reporting requirements.

Measuring methods: Compliance with the stated occupational exposure limits may be checked by occupational hygiene measurements.

Legal basis: EH40/2005 Workplace exposure limits. Last amended January 2020.

PNEC

1H-Benzotriazole (1,2,3), cas-no 95-14-7				
Exposure	Value	Assessment Factor	Extrapolation Method	Note
PNEC aqua (freshwater)	0,0194 mg/l			
PNEC aqua (marine water)	0,0194 mg/l			
PNEC sediment (freshwater)	0,00375 mg/kg			
PNEC sediment (marine water)	0,00375 mg/kg			
PNEC soil	0,003 mg/kg			
PNEC STP (wastewater-treatment facilities)	39,4 mg/kg			

DNEL - workers

1H-Benzotriazole (1,2,3), cas-no 95-14-7					
Exposure	Value	Assessment Factor	Dose Descriptor	Main Impact Parameter	Note

Dermal DNEL (long-term exposure - systemic effects)	1,08 mg/kg				
Inhalation DNEL (long-term exposure - systemic effects)	19 mg/m³				

DNEL - general population

1H-Benzotriazole (1,2,3), cas-no 95-14-7					
Exposure	Value	Assessment Factor	Dose Descriptor	Main Impact Parameter	Note
Oral DNEL (long-term exposure - systemic effects)	0,54 mg/kg				
Dermal DNEL (long-term exposure - systemic effects)	0,54 mg/kg				
Inhalation DNEL (long-term exposure - systemic effects)	9,55 mg/m³				

8.2. Exposure controls

Appropriate engineering controls: Wear the personal protective equipment specified below.

Personal protective equipment, eye/face protection: Wear safety goggles if there is a risk of eye splash. Eye protection must conform to EN 166.

Personal protective equipment, hand protection: Plastic or rubber gloves recommended.

Personal protective equipment, respiratory protection: Not required.

Environmental exposure controls: Ensure compliance with local regulations for emissions.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Parameter	Value/unit
State	Paste
Colour	White
Odour	No data
Solubility	No data

Parameter	Value/unit	Remarks
Odour threshold	No data	
Melting point	No data	
Freezing point	No data	
Initial boiling point and boiling range	> 300 °C	
Flammability (solid, gas)	No data	
Flammability limits	No data	
Explosion limits	No data	
Flash Point	No data	

Auto-ignition temperature	No data	
Decomposition temperature	> 260 °C	
pH (solution for use)	No data	
pH (concentrate)	No data	
Kinematic viscosity	No data	
Viscosity	No data	
Partition coefficient n-octonol/water	No data	
Vapour pressure	< 0.01 hPa	(50 °C)
Density	1.99 g/cm³	(20 °C)
Relative density	No data	
Vapour density	No data	
Relative density (sat. air)	No data	
Particle characteristics	No data	

9.2. Other information

Parameter	Value/unit	Remarks
VOC (Volatile organic compounds):	0 %	

SECTION 10: Stability and reactivity

10.1. Reactivity

Reacts with the following: Alkaline metals/ Acids.

10.2. Chemical stability

The product is stable when used in accordance with the supplier's directions.

10.3. Possibility of hazardous reactions

None known.

10.4. Conditions to avoid

Avoid contact with moisture and water.

10.5. Incompatible materials

Alkaline metals/ Acids.

10.6. Hazardous decomposition products

The product decomposes when combusted or heated to high temperatures and the following toxic gases can be formed: Carbon monoxide and carbon dioxide/ Hydrogen fluoride.

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute toxicity - oral

1H-Benzotriazole (1,2,3), cas-no 95-14-7

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
Rat	LD50		> 5000 mg/kg			

Ingestion may cause discomfort. The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

Acute toxicity - dermal

1H-Benzotriazole (1,2,3), cas-no 95-14-7

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
Rabbit	LD50		> 5000 mg/kg			

The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

Acute toxicity - inhalation

1H-Benzotriazole (1,2,3), cas-no 95-14-7

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
Rat	LC50	3 h	1910 mg/m³			

The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

Skin corrosion/irritation

1H-Benzotriazole (1,2,3), cas-no 95-14-7

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
				Slightly irrittating.		

May irritate the skin - may cause reddening. The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

Serious eye damage/eye irritation

1H-Benzotriazole (1,2,3), cas-no 95-14-7

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
				Irritating		

May cause eye irritation. The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

Respiratory sensitisation or skin sensitisation

1H-Benzotriazole (1,2,3), cas-no 95-14-7

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
Guinea pig	Respiratory sensitisation or skin sensitisation			Non-sensitising	OECD 406	

The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

Germ cell mutagenicity

1H-Benzotriazole (1,2,3), cas-no 95-14-7

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
Mouse In vitro tests.				No indications.	OECD 474	
Microorganisms. In vitro tests.	Ames test			No indications.	OECD 471	

The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

Carcinogenic properties

1H-Benzotriazole (1,2,3), cas-no 95-14-7

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
				Not carcinogenic		

The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

Reproductive toxicity

1H-Benzotriazole (1,2,3), cas-no 95-14-7

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
				No indications.		

The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

Single STOT exposure: The product does not have to be classified. Test data are not available.

Repeated STOT exposure: The product does not have to be classified. Test data are not available.

Aspiration hazard: The product does not have to be classified. Test data are not available.

11.2. Information on other hazards

Endocrine disrupting properties: None known.

Other toxicological effects: None known.

SECTION 12: Ecological information

12.1. Toxicity

1H-Benzotriazole (1,2,3), cas-no 95-14-7

Organism	Species	Exposure time	Test Type	Value	Conclusion	Test method	Source
Fish	Brachydanio rerio		96hLC50	1300 mg/l			
Crustacea	Daphnia magna		24hEC50	200 mg/l			
Crustacea	Daphnia magna		48hEC50	141.6 mg/l			
Algae	Name of species not specified		96hIC50	15.4 mg/l			
Algae	Scenedesmus subspicatus		72hIC50	91 - 141 mg/l			
Bacteria	Pseudomonas putida		3hEC50	> 1000 mg/l			

The product contains small quantities of environmentally hazardous substances. The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

12.2. Persistence and degradability

Not expected to be biodegradable. Test data are not available.

12.3. Bioaccumulative potential

1H-Benzotriazole (1,2,3), cas-no 95-14-7

Organism	Species	Exposure time	Test Type	Value	Conclusion	Test method	Source
			BCF	2.563			
			Log Pow	1.34			

No bioaccumulation expected.

12.4. Mobility in soil

Expected to be mobile in soil. Test data are not available.

12.5. Results of PBT and vPvB assessment

The product does not contain any PBT or vPvB substances.

12.6. Endocrine disrupting properties

None known.

12.7. Other adverse effects

None known.

German water pollution classification (WGK): 1

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Avoid discharge to drain or surface water. If this product as supplied becomes a waste, it does not meet the criteria of a hazardous waste (Dir. 2008/98/EU). Disposal should be in accordance with applicable regional, national and local laws and regulations. Local regulations may be more stringent than regional or national requirements. Empty, cleansed packaging should be disposed of for recycling. Uncleansed packaging is to be disposed of via the local waste-removal scheme.

Category of waste: EWC code: Depends on line of business and use, for instance 13 08 99* wastes not otherwise specified

Absorbent/cloth contaminated with the product: EWC code: 15 02 03 Absorbents, filter materials, wiping cloths and protective clothing other than those mentioned in 15 02 02.

SECTION 14: Transport information

14.1. UN number or ID number:	Not applicable.	**14.4. Packing group:**	Not applicable.
14.2. UN proper shipping name:	Not applicable.	**14.5. Environmental hazards:**	Not applicable.
14.3. Transport hazard class(es):	Not applicable.		

14.6. Special precautions for user

None.

14.7. Maritime transport in bulk according to IMO instruments

Not applicable.

Other Information: The product is not covered by the rules for transport of dangerous goods.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Special Provisions: None.

15.2. Chemical Safety Assessment

Other Information: Chemical safety assessment has not been performed.

SECTION 16: Other information

Version history and indication of changes

Version	Revision date	Responsible	Changes
2.5.0	02/10/2023	Bureau Veritas HSE / DOL	2,9,11

Abbreviations:

PBT: Persistent, Bioaccumulative and Toxic
vPvB: Very Persistent and Very Bioaccumulative
STOT: Specific Target Organ Toxicity
DNEL: Derived No Effect Level
PNEC: Predicted No Effect Concentration

Other Information:

This safety data sheet has been prepared for and applies to this product only. It is based on our current knowledge and the information that the supplier was able to provide about the product at the time of preparation. The safety data sheet complies with applicable law on preparation of safety data sheets in accordance with Regulation 1907/2006/EC “The Registration, Evaluation and Authorization of Chemicals” as amended by the stationary UK REACH etc. (EU Exit) as subsequently changed.

Training advice:

A thorough knowledge of this safety data sheet should be a prerequisite condition.

Classification method:

Calculation based on the hazards of the known components.

Hazard statements

H302 Harmful if swallowed.
H319 Causes serious eye irritation.
H411 Toxic to aquatic life with long lasting effects.

Supplemental hazard information

EUH210 Safety data sheet available on request.

Country:

GB