

When quality counts, count on SKF



Since 1960, we have been producing spindle repairs and modifications with the highest degree of accuracy and quality. This is why so many manufacturers choose SKF to repair their spindles.

You will find a list of the brands of spindles we have repaired on the back. If you have a brand name that isn't listed, chances are that we have repaired it under a different name.



The fastest way back to maximum productivity

Whatever your spindle repair needs, SKF Machine Tool Services has the solution.



We repair all brands and types of high frequency, belt driven, high speed machining and machining center spindles.

Complete in-house manufacturing capabilities allow SKF to manufacture any required replacement parts, providing you with products of highest quality within a reasonable time period.



Turn to the leader

Our engineering and technical personnel can assist you in all your spindle repair, replacement and upgrade requirements.

- Return to maximum productivity
- Turn your "problems" into "profits"



Staff enters arriving spindles into tracking system



Technicians inspect and analyze every component



Experienced machinists rebuild or reproduce any part



Specialists carefully assemble spindles in a clean room

For more information,
contact SKF Solution Factory at

800-589-5563

or visit us on the web at
www.skfusa.com/machinetoolservices



Solution Factory, Cleveland, Ohio



Testing verifies speed, vibration, temperature and critical runouts

SKF Machine Tool Services repairs virtually all spindle brands

Anca	Demer	Hemburg	Lasalle	Pittler/Kessler	Synchron
Abrasive	Denzo	Hemple	Le Blond Makino	Porta	TAC
Accretech	Dependable	Henninger	Leadwell	Porter	Tai-chin
Acroloc	DeVlieg	Herbert Linder	Leico	Pratt Whitney	Taisei
Advance Controls	Diebold	Herbold	Lian Feng	Parker Majestic	Takisawa
Aetna	Diedesheim	Hermle	Lidk Ping	Point	Takumi
Agathon	DMH	Hertlein	Lima	Pope	Taurus
Alfing	Doall	Hillyer	Linco	Precise	TDM
Alpine	Doosan	Himmel	LMT	Puma	Technica
Anayak	DRR	Hitachi	Loh-GMN	Quantum	Tekna
Antralux	Dunham	Hitachi Seiki	M W Hydralink	R O	Tempo
Argo Seiki	Dumore	Holzma	MYL	Rambaudi	Tenco
Arter	Dynamax	Horkos	Maag	Ransburg	Themac
Asahi	Ekstrom Carlson	Homag	Maho	Reid	Thompson
ASC	ELB	Horton	Maka	Reinecker	Thor
ASV	Eldorado	Howa	Manex	Rigid	Tong tai
Atlas	Elite	HSD	Mao Ling	Rivett	Tong Tai Seiki
Auerbach	Elliott	Huffman	Masco	RoboDrill	Topper
Avon	Elmo	Hurco	Master Machine	Rockwell	Tornos
Axxiom	Emco	Hwacheon	Matrix	Roku Roku	Toshiba
Barber Coleman	Enshu	Hydromat	Matsuura	Ross	Tos Hostivar
Barnes	Eurospindle	Ibag	Mattison	Routech	Toyama
Bayer	Everite	Ihara	Maus	Royal Oak	Toyoda
Bertoni & Cotti	Ewag	Ikegai	Max Rawlyer	Rudel	Toyo Kogyo
Behr	Excello	IMC	Mazak	Saimp	Traminer
Benchman	Excellon	IMF	Meiden	SCM	Traub
Berger AG	Fadal	IMP	Mighty Comet	Sakazaki	Tree
Biesse	Faemat	Impco	Miltronics	Samsung	Truflute
Blake	FAG	Incor	Mitsubishi	Savway	TS Precision
Blanchard	Falcon	Index	Mitsui	Schussler	Tschudin
Blohm	Falva	Indramat	Mitsui Seiki	Seco	Tsugami
Boneham & Turner	Fanuc	Intermac	Miyano	Seiko	Taft Pierce
Bowen	Favretto	Invinceable	Monarch	Seiko Seiki	U.S.
Boyer Schultz	Fellows	Ionic	Moore	Setco	UVA
Brembana	Femco	Ingersoll	Morbidelli	SFJ	Ulam
Bridgeport	Femina	J & L	Mori Seiki	Shaper	Unison
Brother	Fischer	Jet	Myford	Sharno	Victor
Brown & Sharpe	Fortuna	Johnford	Nakamura	Sheffield	Vollmer
Bryant	Fortune Victor	Joisten & Kettenbaum	Newall	Shigiya	Voumar
Burkard + Weber	Fosdick	Joke	Nicco	Shinko	Vulcanair
Bullard	Frauenthal	Jones & Lamson	Nichols	Shinks	Van Norman
Campbell	Fryer	Jones & Shipman	Niigata	Shino	Viper
Canton	GA	Jung	Niles	Shizuoka	Wadkin
Carlton	G & L	Junkers	Nippe	Shoda	Wagner
Carver	Gallmeyer & Livingston	K O Lee	Nippon	Siarto	Waida
Celoschi	Gamfi	Kaiser	Nishida	Sicar	Walter
Chevalier	Gardner	Kapp	Normac	Siga	Ward
Chiron	Gildemeister	Kasper	Norton	Sigma	Wardell
Churchill	Gilman	Kellenberger	NSK	Simplex	Wasino
Cincinnati	Giordano Colombo	Keller	NSP	Sintex	Wedalco
Cinex	Gleason	Kent	NTC	Sjogren Saginaw	Weisser
Citizen	GMN	Kenward	Oberg	SKF	Wendt
Cleerman	GMS	Kessler	Oerlikon	SMG	Wheellabrador
Cleveland	Gomiya	Ketterer	Okamoto	SNK	White Sunstrand
CMS	Gorton	Kia	OKK	Sopko	Wit-o-Matic
Coborn	Grisetti	Kikinda	Okuma	Spintec	Wickman Sheffield
Coburn	Grob	Kindt Collins	Oliver	Springfield	Willemin
Colmatic	Gros-ite	Kingsbury	Olofsson	Stama	Woods
Colombo	H & D	Kitagawa	OMC	Standard	Whitnon
Combing	HSD	Kitako	Omlat	Steinel	Yachyio
Comec	Haas	Kitamura	Onsrud	Sticker	YAM
Covel	Hamai	Kiwa	Ooya	Stoffel	Yamage
Cyclone	Hardinge	Klingelberg	Orion	Strausak	Yamaguchi
Cytec	Harig	Kolb	Overbeck	Studer	Yamashita
DAC	Haril	Komo	Paatz	Sugino	Yamazaki
Daewoo	Harvill	Kondia	Parker	Suhner	Yang
Dainichi	Hauser	Koyer	Pangborn	Summit	Yaskawa
Danieli	Heald	Kruger	PBA	Sunmax	YCI
Dankaert	Heathway	Kumer	PBS	Sunstrand	Yougi
Danobat	Heian	Kuraki	Peron	Sun Tool	
Dearborn	Heller	Lamb	Perske	Supermax	
Deckel		Landis	Piat	Swiss Lathe	

© SKF is a registered trademark of SKF USA Inc.

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of use of the information contained herein.

