


2.2 DPV profile piston seals, inch sizes

D 1 – 6.002 in.



Maximum extrusion gap e

Radial Series e_{\max} at 80 °C (175 °F)
depth for pressures
S 2 300 psi 3 600 psi 5 800 psi

in.	–	in.
0.125	2	0.012
0.187	3	0.018
0.25	4	0.022

For additional information → page 34

2.2

Dimensions

Designation

D +0.002	d	Tolerance	L +0.005	S	R max.	C min.	Designation
1	0.758	-0.002	0.187	0.125	0.02	0.125	DPV-210-KOM
1.5	1.258	-0.002	0.187	0.125	0.02	0.125	DPV-218-KOM
1.75	1.508	-0.002	0.187	0.125	0.02	0.125	DPV-222-KOM
2	1.63	-0.002	0.281	0.187	0.025	0.156	DPV-326-KOM
2.25	1.88	-0.002	0.281	0.187	0.025	0.156	DPV-328-KOM
2.5	2.13	-0.002	0.281	0.187	0.025	0.156	DPV-330-KOM
2.75	2.38	-0.002	0.281	0.187	0.025	0.156	DPV-332-KOM
3	2.63	-0.002	0.281	0.187	0.025	0.156	DPV-334-KOM
3.5	3.13	-0.002	0.281	0.187	0.025	0.156	DPV-338-KOM
3.75	3.38	-0.002	0.281	0.187	0.025	0.156	DPV-340-KOM
4	3.63	-0.002	0.281	0.187	0.025	0.156	DPV-342-KOM
4.5	4.13	-0.002	0.281	0.187	0.025	0.156	DPV-346-KOM
5	4.63	-0.002	0.281	0.187	0.025	0.156	DPV-350-KOM
5.502	5.028	-0.004	0.375	0.25	0.032	0.187	DPV-429-KOM
6.002	5.528	-0.004	0.375	0.25	0.032	0.187	DPV-433-KOM

Other sizes are available on request