Flow Monitors and Sensors

for intermittent and circulating centralized lubrication systems







Flow monitors/sensors have the task of monitoring the flow of lubricant from the pump or a piston distributor element to the lube point. Flow monitors with various designs are used for this job. A further task involves monitoring a continuous flow of oil from a pump through a lubrication system. These flow monitors are designed for a throughput ranging from 0,5 cm³ to 14 000 cm³.

Flow sensors keep an eye on the flow of lubricant from a metering point to the lube point, the metering point metering out a small amount of oil for only a short period of time.

Depending on the type, flow sensors can monitor lubricant quantities ranging from 10 mm³ all the way to 600 mm³ per lubricant pulse.

The oil-streak sensors monitor the continuity of the oil flow in oil+air systems.

So the following points have to be observed when selecting an appropriate monitoring device:

- intermittent or continuous operation
- kind of lubrication system
- · lubricant quantity to be monitored
- eff. viscosity of the lubricant
- system pressure.




Overview flow monitors and -sensors

Please have a look at the important product usage information on the back cover of the brochure.

Designation	Order No.	Metered quantity flow rate	Application	Port A	Port B	Fig	Page
Flow monitor	171-100-011	$0.2 - 1.5 \text{ cm}^3/\text{pass}$	Intermittend totalloss lubrication systems	M10×1	M18×1,5	1	2
Flow monitor	171-210-051 171-210-052 171-210-053 171-210-054 171-210-055	50 - 100 100 - 200 200 - 500 cm ³ /min 500 - 800 800 - 1800	Circulating centralized lubrication systems	M10×1	M18×1,5	2	3
Flow monitor	171-210-061 171-210-062 171-210-063 171-210-064 171-210-065	1,6 - 2,5 2,3 - 4,0 3,6 - 6,0 l/min 5,5 - 10,0 8,0 - 14,0	Circulating centralized lubrication systems	M18×1,5	M18×1,5	3	3
Flow sensor	GS300 GS304N GS304P	10 – 600 mm ³ /lmpuls	Intermittend centralized lubrication system e.g. with piston distributors, metering elem		oilers	4	8
Oil-streak sensor	GS4011-S20 GS6011-S20 GS4011-S50 GS6011-S50	120 - 600 120 - 600 60 - 120 mm ³ /h 60 - 120	Oil+air centralized lubrication systems for assembling very close to the lube point		5	9	
Oil-streak sensor	GS4011-S300 GS6011-S300	ab 2 mm³/Impuls	Oil+air centralized lubrication systems for assembling very close to the mixing valve		5	9	
Please note: See leaflet 1-1730-EN for associated line sockets.							

Flow monitors for monitoring of an intermittend flow of oil

Totalloss lubrication systems




Technical data	
Number of cycles	
Materials: Housing die-cast zinc, polyamide Seals NBR (FKM version on request)	
³) Suitable for medial operating viscosity. In case of higher viscosity decreases the number of cycles.	
4) In single line centralized lubrication systems the main line needs to have before the distributors a pressure of at least 14 bars.	

Order No.	Flow rate
171-100-011	0,2 – 1,5 cm³/pass


Flow monitors for the monitoring of a continuous flow of oil

circulating lubrication systems with 50 bis 1800 cm³/min or 1,6 bis 14 l/min



Technical data
Operating viscosity 20 – 1000 mm ² /s
Actuating pressure min. 4 bars ³), max. 25 bars
Electr. switching changeover 250 V AC, 0,5 A
Perm. operating temperature + 5 bis +80 °C
Type of enclosureIP 65
Mounting position any
Materials:
Housing die-cast zinc, polyamide
Seals NBR (FKM version on request)
3) If the flow monitors are equipped with metering restrictors, at least 6 bars are required in the feed lin

Order No. (Fig. 2)	Flow rate
171-210-051	50 – 100
171-210-052	100 – 200
171-210-053	200 – 500 cm³/min
171-210-054	500 – 800
171-210-055	800 – 1800




Order No. (Fig. 3)	Flow rate
171-210-061	1,6 - 2,5
171-210-062	2,3 - 4,0
171-210-063	3,6 – 6,0 l/min
171-210-064	5,5 – 10,0
171-210-065	8,0 – 14,0

1) Port tapped for cutting-sleeve screw union E0-2 DIN 2353 / ISO 8434-1


²) DIN 2353/ISO 8434-1. Only permissible for the use of preassembled fittings. We recommend use of a preassembled E0-2 screw union. (Example: GA21...23/GA30)


System examples and connection fittings


I. Singleline, totalloss lubrication system with piston distributors





II. Circulating lubrication system with multicircuit pump unit












System examples and connection fittings

${\ensuremath{\mathsf{III}}}.$ Circulating lubrication system with restrictors

$\ensuremath{\text{IV.}}$ Circulating lubrication system with restrictor tubes




				Connect	tion fittings III
Connection Straight scr	-	vith restricto	or ²)		
Connection	for tubing diam.	Union nut order No.	Cutting sleeve order No.	Adapter with (compl. with order No.	
А3	6	406-302	406-301	GD60 GD61 GD62 GD63 GD64 GD65	60 61 62 63 64 65
A3	8	408-302	408-301	GD80 GD81 GD82 GD83 GD84 GD85 GD86 GD87 GD88 GD89	80 81 82 83 84 85 86 87 88

Connection	Code /
A3	
	The required restrictor sizes are determined with the nomograph on page 6


Connection fit	Connection fittings IV					
	Only for a range of 1.6 to 14 l/min (flow monitor as per Fig. 2, page 3)					
	Tube union ²) for direct connection to the flow monitor					
Connection	for tubing diam.	Function nut order No.				
A4	12	460-212-001				
4.						

- Port tapped for solderless tube connection
 Port tapped for solderless cutting-sleeve screw union to DIN 2353



Nomograph for determination of restrictor sizes


(connection A3, system example III)



Determining the restrictor size

- 1. Draw a straight line along the index lines through point ${\bf Q}\ \nu$ effective.
- 2. Determine the point at which **p** intersects with this line, resulting in **D**.
- 3. Select the restrictor **closest** to point **D.**

D must be inside the white field, that means small amounts cannot be "apportioned and monitored" with the unit.



Example 1:

required: Q = $36 \text{ cm}^3/\text{min}$, given: $v \text{ eff.} = 280 \text{ mm}^2/\text{s}$

p = 7 bars

Result: restrictor size No. 60

(borderline case)




Example 2:

required: Q = $260 \text{ cm}^3/\text{min}$, given: $v \text{ eff.} = 480 \text{ mm}^2/\text{s}$


p = 8 bars

Result: restrictor size No. 80




Flow rate at activation point as a factor of the viscosity

Flow monitors to monitor a flow of oil (circulating lubrication system)




Order No.	Flow rate activation point [cm³/min]	Actuation curve as per diagram
171-210-051 171-210-052 171-210-053 171-210-054 171-210-055	35 75 150 400 700	① ② ③ ④ ⑤



Order No.	Flow rate activation point [l/min]	Actuation curve as per diagram
171-210-061 171-210-062 171-210-063 171-210-064 171-210-065	1.3 1.9 3.0 4.5 6.5	① ② ③ ④ ⑤

GS300, GS304N, GS304P

Flow sensors for monitoring of lubricant feedright at the lube point



- 1) Port tapped for solderless 4 mm diam. tube connection
- ²) Accessories GS300: 5 m connection cable, order No. GS200.U4 GS304P / GS304N: 5 m onnection cable with straight line socket, 4-pole type, order No. 179-990-600

Technical data

Measuring principle..... calorimetrical

Suitable metered quantities $\,\ldots\,$ from 0.01 to 0.6 cm 3 /pulse

Clock frequency³) max. 4 pulse/min

Lubricant⁴)..... oil and grease, NLGI grades 000, 00

Max. operating pressure 40 bars

Operating temperature +10 °C to +50 °C

- ³) Sensor needs 30 sec. of warmup time.
- 4) The use of lubricants containing corrosive and/or abrasive additives may impair sensor function and possibly damage the sensor.

Electrical data

Load current $\rm I_A$ for GS300 $\ \ldots \ max. \ 10 \ mA$

for GS304 max. 500 mA per output

Output protection short-circuit protection


Built-in plug circular connector

with M12×1 screw plug

Order No.		Switching function		Electrical connection
GS300	1 — 1 mA 4 — 10 mA PNP 3 — 3	Pin 1 (BN - brown): Pin 3 (BU - blue): Pin 4 (BK - black):	+ 24 V 0 V PNP/NO – closes in event of flow	$ \begin{array}{cccccccccccccccccccccccccccccccccccc$
GS304P	1 + + 2 - + + + + + + + + + + + + + + + +	Pin 1 (BN - brown): Pin 2 (WH Pin 3 (BU - blue): Pin 4 (BK - black):	+ 24 V - white): 0 V PNP/NO – closes in event of flow	PNP/NC – opens in event of flow
GS304N	1 + 2 - + 4 3	Pin 1 (BN - brown): Pin 2 (WH Pin 3 (BU - blue): Pin 4 (BK - black):	+ 24 V - white): 0 V NPN/NO – closes in event of flow	1 2 NPN/NC – opens in event of flow

GS4011-S.., GS6011-S..

The oil-streak sensors monitor the continuity of the oil flow in oil+air lubrication systems



So-called oil+air centralized lubrication systems are used to supply high-speed rolling bearings in tool spindles. The bearings are supposed to be supplied with extremely small quantities of lubricant (minimal-quantity lubrication) in the case of these applications. To achieve such small quantities of oil per unit of time, what was originally a relatively large drop of oil is torn apart by a current of air on its way from the metering point to the bearing. The oil to be delivered is fed in the line to the bearing as a thin flow of lubricant along the wall.

Monitoring:

So far, only the metered quantity of oil from the metering element has been checked upstream of the oil and air mixing point. The oil-streak sensor makes it possible to monitor the transport of a fine current of oil along the secondary line's wall downstream of the oil and air mixing point. The closer the sensor is located to the lube point, the more reliable the system monitoring.

Technical data

Measuring principle......optical
Fluidoil + air
Max. operating pressure10 bars
Operating temperature0 to +60 °C
Mounting positionhorizontal, no swivel drive
(GS4011-S300 and GS6011-S300 also vertical)

Electrical data

Ra	ated voltage U _N
0	perating range U _B
М	ax. power consumption I _E 40 mA
Ty	/pe of enclosure
0	utputs pnp type
	closes when oil streaks detected, opens when there are none

Color coding with standard sensor cables:

brown (BN)	+24 V
blue (BU)	GND
black (BK)	make contact
white (WH)	break contact

1) Protective measure to be taken for operation in conformity with "Functional Extra-Low Voltage with Safety Separation" (PELV = Protective Extra-Low Voltage)

Accessories:

Connection cable with straight cable socket, 4-pole type, length 5 m, order No. 179-990-600
Socket, 90° angled, order No. 179-990-372

Plastic tubing ø D	Flow rate
4	120 – 600 mm³/h
4	60 – 120 mm³/h
6	120 – 600 mm³/h
6	60 – 120 mm³/h
4	from 2 mm ³ /pulse
6	from 2 mm ³ /pulse
	4 4 6 6

Flow Monitors and Sensors Notes

Order No. 1-1704-EN

Subject to change without notice! (03/2021)

Important product usage information

All products from SKF may be used only for their intended purpose as described in this brochure and in any instructions. If operating instructions are supplied with the products, they must be read and followed. Not all lubricants are suitable for use in centralized lubrication systems. SKF does offer an inspection service to test customer supplied lubricant to determine if it can be used in a centralized system. SKF lubrication systems or their components are not approved for use with gases, liquefied gases, pressurized gases in solution and fluids with a vapor pressure exceeding normal atmospheric pressure (1013 mbars) by more than 0.5 bar at their maximum permissible temperature.

Hazardous materials of any kind, especially the materials classified as hazardous by European Community Directive EC 67/548/EEC, Article 2, Par. 2, may only be used to fill SKF centralized lubrication systems and components and delivered and/or distributed with the same after consulting with and receiving written approval from SKF.

Further brochures:

1-0103-EN Fittings and Accessories

1-1730-EN Electric Plug-and-Socket Connectors

1-9201-EN Transport of Lubricants in Centralized Lubrication Systems

SKF Lubrication Systems Germany GmbH

Motzener Strasse 35/37 · 12277 Berlin · Germany PF 970444 · 12704 Berlin · Germany Tel. +49 (0)30 72002-0 · Fax +49 (0)30 72002-111 www.skf.com/lubrication

Thi	This brochure was presented by:						

® SKF is a registered trademark of the SKF Group.

© SKF Group 2021

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

