


Turbulo-MPB

Bilge Water Separator



General description

- Turbulo-MPB (Mechanical Phase Breaker) designed, type-tested and approved pursuant to resolution MEPC 107(49)
- TMPB fulfils 5ppm criteria
- TMPB can treat oil/water-mixtures and emulsions pursuant to resolution MEPC 107(49)
- 6 capacities: 0.25 / 0.5 / 1.0 / 2.5 / 5.0 / 10.0 m³/h
- BWS is pressure type – pump can be installed as loose supply for new building and retro-fitting
- No use of chemicals or charcoals



- 1 **Control switch box** – Operational controls and alarm cabinet for safe and easy handling.
- 2 **Dry-run protection** – Avoids dry-running of the pump.
- 3 **Helical rotary pump with low r/min** – Feeds the bilge water into the 1st stage of the separator.
- 4 **1st stage: High efficiency coalescer (HEC)** – Retention of bigger solids, free oil and separation of oil by coalescence. The HEC is cleanable.
- 5 **Oil-level probe** – Detects oil level in the 1st stage for automatic discharging.
- 6 **Heating device** – Heats the oil for optimised oil discharge.
- 7 **Oil discharge valve** – Automatic oil discharge initialised by the oil-level probe.
- 8 **2nd stage: Deep-filtration unit** – Protection of 2nd stage HycaSep elements by permanently reducing the solid matter concentration and to some extent the turbidities.
- 9 **2nd stage: HycaSep element for retention of finest oil droplets** – Securing the required oil content (ppm) at the effluent before passing the oil content monitor to overboard.
- 10 **Bilge alarm (Tamper-proofed oil content monitor)** – Permanent monitoring of cleaned bilge water. Ensures 18-month recording according to MEPC.
- 11 **Sea/bilge valve** – Solenoid valve for routing of water to overboard or recirculation to bilge tank. Manual valve for port state testing.
- 12 **Skit frame** – Fully assembled and delivered skit mounted for easy installation.
- 13 **Analogue pressure gauges** – Visualisation of pressure conditions for monitoring and maintenance.
- 14 **1st and 2nd stage isolation valve** – Maintenance-friendly, draining of 1st or 2nd stage.
- 15 **Cover plate of 1st and 2nd stage** – Access to all components by removing the top plates. No piping to be removed, for easy service access.
- 16 **Pressure safety valve** – Prevents overpressurisation of the pressure vessel.



Ex-proof design




Booster pump design

Applications

- Ex-proof design for hazardous areas
- Booster pump for higher counter-pressure
- NORSOK standard
- Special coating and design
- Taylor-made design on customer demand
- Shock-proof design on demand
- Own laboratory
- NR 13

Technology





Advantages

Design

- Compact two-stage separator – reliable separation of oily mixtures in a capacity range of 0.25 m³/h to 10 m³/h
- Type approval pursuant to IMO Resolution MEPC 107.(49) issued by: USCG; CCS; RMRS; BG Verkehr
- Fulfills special requirements such as the 5ppm criteria for: Environmental passport (GL) / Clean Design (DNV) / Canadian Coast Guard (CCG)
- Oil content monitor – type-tested and approved pursuant to IMO Resolution MEPC.107(49)
- MARPOL: Sea to bilge (three-way valve)
 - Safe routing of clean water overboard or back to bilge or holding tank. Manual valve for testing when requested by port state control.

Installation

- Reliable components and DIN ISO 9001/MED certified production process at SKF Marine
- Final manufactured unit, fully tested and delivered ready-to-use to any shipyard worldwide
- Retrofit and customized solutions available:
 - Small footprint
 - Easy to install - skit mounted for convenient handling
 - Simplified installation procedure
 - No OEM commissioning engineer necessary
 - No chemicals required for commissioning

Operation

- Reliable and operator-friendly technology:
 - Automatic operation (oil drain by level electrode / discharge by pneumatic oil discharge valve)
 - Continuous oil-content measuring and status recording
 - Approved alarm and monitoring concept
 - Dry-run protection of pump
- Operator-friendly maintenance and handling:
 - Easy access to inside of separator from top
 - No need to dismantle pipes and fittings
 - Precise condition monitoring and condition-based maintenance of elements
- Low operational costs:
 - No chemicals, charcoals or absorber
 - No sludge through chemicals
 - No back-flushing required (low freshwater consumption)
 - Protection of top HycaSep elements

Service

- Documentation for TMPB:
 - Simple and clear installation and commissioning procedure
 - Operating instructions
 - Troubleshooting advice
 - Type approval and test certificates in accordance with requirements
- Worldwide service network and availability of spares and consumables

SKF Marine GmbH

Hermann-Blohm-Straße 5
20457 Hamburg, Germany

skf.com | skf-marine.com

© SKF and Turbulo are registered trademarks of the SKF Group.

© SKF Group 2016

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

PUB 43/P2 14706/2 EN · April 2016

Certain image(s) used under license from Shutterstock.com.