

# Safety data sheet

Version: 02.02/USA

---

## SECTION 1: Identification

### 1.1. Product identifier

Trade name: LGGB 2

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended uses: Lubricant Lubricating grease

For Chemical Emergency  
Spill, Leak, Fire, Exposure, or Accident  
Call CHEMTREC Day or Night  
Within USA and Canada: 1-800-424-9300  
Outside USA and Canada: +1 703-527-3887 (collect calls accepted)

Location:  
CHEMTREC  
2900 Fairview Park Drive  
Falls Church VA 22042-4513  
USA

### 1.3. Details of the supplier of the safety data sheet

Supplier: SKF MAINTENANCE PRODUCTS  
Postbus 1008  
NL-3430 BA Nieuwegein  
The Netherlands  
Tel: +31 30 6307200  
Email: sebastien.david@skf.com  
WWW: www.skf.com

### 1.4. Emergency telephone number

+31 30 6307200

---

## SECTION 2: Hazards identification

### 2.1. Classification of the substance or mixture

Classification:

The product shall not be classified as hazardous according to the national classification and labelling rules.

Most serious harmful effects:

May cause slight irritation to the skin and eyes.

### 2.2. Label elements

The product shall not be classified as hazardous according to the national classification and labelling rules.

### 2.3. Other hazards

None known.

---

## SECTION 3: Composition/information on ingredients

### 3.2. Mixtures

CAS No.	Substance	w/w%	Note
	Contains no substances subject to disclosure requirements.		

#### SECTION 4: First aid measures

##### 4.1. Description of first aid measures

Inhalation:	Seek fresh air. Seek medical advice in case of persistent discomfort.
Ingestion:	Wash out mouth thoroughly and drink 1-2 glasses of water in small sips. Seek medical advice in case of discomfort.
Skin:	Remove contaminated clothing. Wash skin with soap and water. Seek medical advice in case of persistent discomfort.
Eyes:	Flush with water (preferably using eyewash equipment) until irritation subsides. Seek medical advice if symptoms persist.
Other information:	Bring the safety data sheet or label when seeking medical advice

##### 4.2. Most important symptoms and effects, both acute and delayed

May cause slight irritation to the skin and eyes.

##### 4.3. Indication of any immediate medical attention and special treatment needed

Treat symptoms. No special immediate treatment required.

#### SECTION 5: Fire-fighting measures

##### 5.1. Extinguishing media

Suitable extinguishing media	Extinguish with powder, foam, carbon dioxide or water mist. Use water or water mist to cool non-ignited inventory.
Unsuitable extinguishing media	Do not use a jet of water, as it may spread the fire.

##### 5.2. Special hazards arising from the substance or mixture

Not flammable, but combustible. Product decomposes in fire conditions or when heated to high temperatures, and inflammable and toxic gases may be released.

##### 5.3. Advice for firefighters

Move containers from danger area if it can be done without risk. Avoid inhalation of vapor and smoke gases – seek fresh air. Wear Self-Contained Breathing Apparatus (SCBA) with chemical resistant gloves.

#### SECTION 6: Accidental release measures

##### 6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel:	Wear safety goggles if there is a risk of eye splash. Wear gloves.
For emergency responders:	In addition to the above: Normal protective clothing is recommended.

##### 6.2. Environmental precautions

Prevent spillage from entering drains and/or surface water.

##### 6.3. Methods and material for containment and cleaning up

Contain and absorb spills using sand or other absorbent material and transfer to suitable waste containers. Wipe up minor spills with a cloth. Rinse with water.

##### 6.4. Reference to other sections

See section 8 for type of protective equipment. See section 13 for instructions on disposal.

#### SECTION 7: Handling and storage

##### 7.1. Precautions for safe handling

The product should be used under well-ventilated conditions and preferably under process ventilation. Running water and eye wash equipment should be available. Wash hands before breaks, before using restroom facilities, and at the end of work.

##### 7.2. Conditions for safe storage, including any incompatibilities

The product should be stored safely, out of reach of children and away from food, animal feed, medicines, etc. Do not store with the following: Strong oxidisers/ Strong acids/ Strong alkalis.

##### 7.3. Specific end use(s)

None.

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

Legal basis: ACGIH Threshold Limit Values (TLV's) and Biological Exposure Indices (BEI's), 2017. OSHA 29 CFR part 1910.1000, table Z1-Z3, Limits for Air Contaminants 2006.

Contains no substances subject to disclosure requirements.

### 8.2. Exposure controls

Appropriate engineering controls: Wear the personal protective equipment specified below.

Personal protective equipment, eye/face protection: Wear safety goggles if there is a risk of eye splash.

Personal protective equipment, skin protection: Wear gloves. Type of material and thickness: Nitril rubber.  $\geq 0,38\text{mm}$  Penetration time:  $>8$  hours.

Personal protective equipment, respiratory protection: Not required.

Environmental exposure controls: Ensure compliance with local regulations for emissions.

---

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

State: Paste /Fat.  
Color: Light brown  
Odour: Characteristic  
Odour threshold: No data  
pH (solution for use): No data  
pH (concentrate): No data  
Melting point/freezing point: No data  
Initial boiling point and boiling range: No data  
Flash point: No data  
Evaporation rate: No data  
Flammability (solid, gas): No data  
Upper/lower flammability limits: No data  
Upper/lower explosive limits: No data  
Vapor pressure: No data  
Vapour density: No data  
Relative density: 0,87 (77 °F)  
Solubility: Insoluble in the following: Water.  
Partition coefficient n-octanol/water: No data  
Auto-ignition temperature: No data  
Decomposition temperature: No data  
Viscosity: No data  
Explosive properties: No data  
Oxidizing properties: No data

### 9.2. Other information

NLGI: 2

---

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

Reacts with the following: Strong oxidisers/ Strong acids/ Strong alkalis.

### 10.2. Chemical stability

The product is stable when used in accordance with the supplier's directions.

### 10.3. Possibility of hazardous reactions

None known.

### 10.4. Conditions to avoid

Avoid heating and contact with ignition sources.

### 10.5. Incompatible materials

Strong oxidisers/ Strong acids/ Strong alkalis.

### 10.6. Hazardous decomposition products

Product decomposes in fire conditions or when heated to high temperatures, and inflammable and toxic gases may be released.

---

## **SECTION 11: Toxicological information**

### **11.1. Information on toxicological effects**

Acute toxicity - oral:	The product does not have to be classified. Test data are not available. Ingestion of large quantities may cause discomfort.
Acute toxicity - dermal:	The product does not have to be classified. Test data are not available.
Acute toxicity - inhalation:	The product does not have to be classified. Test data are not available.
Skin corrosion/irritation:	The product does not have to be classified. Test data are not available. Degreases the skin. Long-term exposure may cause irritation and possible infection.
Serious eye damage/eye irritation:	The product does not have to be classified. Test data are not available. Temporary irritation.
Respiratory sensitisation or skin sensitisation:	The product does not have to be classified. Test data are not available.
Germ cell mutagenicity:	The product does not have to be classified. Test data are not available.
Carcinogenic properties:	The product does not have to be classified. Test data are not available.
Reproductive toxicity:	The product does not have to be classified. Test data are not available.
Single STOT exposure:	The product does not have to be classified. Test data are not available.
Repeated STOT exposure:	The product does not have to be classified. Test data are not available.
Aspiration hazard:	The product does not have to be classified. Test data are not available.
Other toxicological effects:	On warming/heating, the vapours emitted may cause irritation to the respiratory organs. May cause coughing and breathing difficulties.

---

## **SECTION 12: Ecological information**

### **12.1. Toxicity**

The product does not have to be classified according to GHS (Globally Harmonized System of Classification and Labelling of Chemicals). Test data are not available.

### **12.2. Persistence and degradability**

Test data are not available.

### **12.3. Bioaccumulative potential**

Test data are not available.

### **12.4. Mobility in soil**

Test data are not available.

### **12.5. Results of PBT and vPvB assessment**

No assessment has been made.

### **12.6. Other adverse effects**

Forms an oil film on water surfaces that may harm aquatic organisms and may disturb the transport of oxygen at the air-water interface.

German water pollution classification (WGK): 1

---

## **SECTION 13: Disposal considerations**

### **13.1. Waste treatment methods**

Avoid discharge to drain or surface water. If this product as supplied becomes a waste, it meets the criteria of a hazardous waste as defined under the Resource Conservation and Recovery Act (RCRA) 40 CFR 261.

Disposal should be in accordance with applicable regional, national and local laws and regulations. Local regulations may be more stringent than regional or national requirements. Uncleansed packaging is to be disposed of via the local waste-removal scheme. Empty, cleansed packaging should be disposed of for recycling.

---

**SECTION 14: Transport information**

The product is not covered by the rules for transport of dangerous goods.

- 14.1. UN number -
- 14.2. UN proper shipping name -
- 14.3. Transport hazard class(es) -
- 14.4. Packing group -
- 14.5. Environmental hazards -
- 14.6. Special precautions for user -

**14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code**

-

---

**SECTION 15: Regulatory information****15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

Special provisions: None.

**NFPA ratings (scale 0 - 4)**

Health Hazard: 0

Flammability: 1

Instability: 0

**HMIS III ratings (scale 0 - 4)**

Health hazard: 0

Flammability: 1

Physical hazard: 0

---

**SECTION 16: Other information**

Changes have been made in the following sections: 8,16

Abbreviation explanations: PBT: Persistent, Bioaccumulative and Toxic vPvB: Very Persistent and Very Bioaccumulative  
STOT: Specific Target Organ Toxicity

Classification method: Calculation based on the hazards of the known components.

Training: A thorough knowledge of this safety data sheet should be a prerequisite condition.

Other information: This safety data sheet has been prepared for and applies to this product only. It is based on our current knowledge and the information that the supplier was able to provide about the product at the time of preparation. The safety data sheet complies with applicable law on preparation of safety data sheets in accordance with CFR29, §1910.1200.

Revision: 10-03-2018

Replaces: 27-11-2015

---