

Why SKF?

SKF Explorer spherical roller bearings for vibratory applications



Common applications

- Vibrating screens
- Compactors
- Road rollers

User benefits

- Lower operating temperatures
- Increased bearing service life
- Improved wear and contamination resistance
- Excellent high speed performance
- Reduced risk of fretting corrosion and induced axial preload (VA406)

By design, SKF spherical roller bearings can accommodate very heavy radial and heavy axial loads in applications prone to misalignment or shaft deflections. In addition, SKF spherical roller bearings for vibratory applications are designed to accommodate very high vibration levels.

SKF Explorer spherical roller bearings provide a significant improvement in key operational parameters. These bearings are so robust that they can last several times longer than other spherical roller bearings under typical heavy-duty conditions.

Upgraded self-aligning SKF Explorer bearings

All SKF Explorer spherical roller bearings have been upgraded to a new level of performance, featuring a combination of high-quality steel and an improved heat treatment. Upgraded SKF Explorer spherical roller bearings provide longer service life, particularly in applications where there are high levels of contamination or poor lubrication conditions.


Product features

- Designed for high vibration levels
- Made of super-clean and tough upgraded steel
- Reduced dimensional tolerances
- Special cage design
- C4 Clearance as standard
- Available with a PTFE coated bore (designation suffix VA406)



Diagram 1

Relative wear for different bearing steel




Test conditions

Lubricant: Turbo T 68 mineral oil containing 3 g/l of cast iron powder
 $\kappa = 1,2$
 $C/P = 3,4$

Speed: 525 r/min
 Running time: 72 h
 All components were weighed before and after the test

Diagram 2

Service life under poor lubrication conditions




Test conditions

Bearings: 22220 E
 Load: 140 kN
 Speed: 1 500 r/min

Lubricant: Turbo T 9 mineral oil
 $\kappa = 0,45$
 Temperature: 75 °C

Diagram 3

Service life under contaminated conditions




Test conditions

Bearings: 22220 E
 The bearings were run-in under contaminated conditions.
 $\eta_c = 0,2$

Operating conditions after cleaning
 Load: 140 kN
 $C/P = 3,0$
 Speed: 1 500 r/min
 Lubricant: Turbo T 68 mineral oil
 $\kappa = 2,1$

Upgraded SKF Explorer spherical roller bearings

Upgraded SKF Explorer spherical roller bearings are identified on the packaging, and the bearing outer rings are marked "WR".



Test conditions

Test results of SKF Explorer performance class spherical roller bearings compared to competitor bearings.
 Bearing basic designation: 22220
 Sample: 35 bearings per brand
 Load: 140 kN
 $C/P = 3,0$
 $\kappa = 1,76$
 Speed: 1 500 r/min



A complete assortment for vibratory applications

SKF offers spherical roller bearings for vibratory applications in the 223-series, identified with suffix VA405, or VA406 (PTFE coated cylindrical bore).

Table 1

SKF Explorer spherical roller bearings for vibratory applications

d	Bearing	VA405	VA406
mm			
40	22308	•	
45	22309	•	
50	22310	•	
55	22311	•	
60	22312	•	
65	22313	•	
70	22314	•	
75	22315	•	•
80	22316	•	•
85	22317	•	•
90	22318	•	•
95	22319	•	•
100	22320	•	•
110	22322	•	•
120	22324	•	•
130	22326	•	•
140	22328	•	•
150	22330	•	•
160	22332	•	•
170	22334	•	•
180	22336	•	•
190	22338	•	•
200	22340	•	•
220	22344	•	

© SKF and SKF EXPLORER are registered trademarks of the SKF Group.

© SKF Group 2013

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

PUB BU/P9 06551/1 EN · September 2013

