

# SKF Ecorubber-H

*Hydrogenerated acrylonitrile-butadiene-rubber*

DIN/ISO: H-NBR

ASTM: H-NBR

Property	Unit	Value	Standard
Standard color	–	Black	■
Durometer hardness	Shore A	85 ±5	DIN ISO 7619
Density	g/cm <sup>3</sup>	1,23 ±0,02	DIN EN ISO 1183-1
Tensile strength	MPa	≥ 18	DIN 53504
Elongation at break	%	≥ 180	DIN 53504
100% modulus	MPa	≥ 10	DIN 53504
Compression set 100 °C / 24 h	%	≤ 22	DIN ISO 815
Tear strength	N/mm	24	DIN ISO 34-1
Abrasion	mm <sup>3</sup>	90	DIN ISO 4649
Swelling behavior ASTM Oil No. 1, 70 h / 100 °C			
Change in durometer hardness	Shore A	+6	DIN ISO 7619
Volume change	%	-8	DIN 53521
ASTM Oil No. 3, 70 h / 100 °C			
Change in durometer hardness	Shore A	-8	DIN ISO 7619
Volume change	%	+11	DIN 53521
Swelling behavior, wet			
Change in durometer hardness	Shore A	0	DIN ISO 7619
Volume change	%	+2,5	DIN 53521
Heat resistance, air 70 h / 150 °C			
Change in durometer hardness	Shore A	+5	DIN ISO 7619
Volume change	%	0	DIN 53521
Minimum service temperature	°C	-25	–
Maximum service temperature	°C	+150	–

IMPORTANT NOTE: The values shown above are only valid for material samples prepared for test purposes according to the stated standards. The values, which are marked with the symbols greater than or equal to (≥) and smaller than or equal to (≤), are nominal values and must be fulfilled for each batch. These values are tested on selected samples.

© SKF is a registered trademark of the SKF Group.

© SKF Group 2014

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

PUB SE/P8 12482/1 EN · October 2014

