

# SKF High load, extreme pressure bearing grease

## LGEP 2

SKF LGEP 2 is mineral oil based, lithium soap thickened grease with extreme pressure additives. This grease provides good lubrication in general applications subjected to harsh conditions and vibrations.

- Excellent mechanical stability
- Extremely good corrosion inhibiting properties
- Excellent EP performance

### Typical applications

- Pulp and paper making machines
- Jaw crushers
- Dam gates
- Work roll bearings in steel industry
- Heavy machinery, vibrating screens
- Crane wheels, sheaves
- Slewing bearings



### Available pack sizes

Packsizes	Designation
420 ml cartridge	LGEP 2/0.4
1 kg can	LGEP 2/1
5 kg can	LGEP 2/5
18 kg pail	LGEP 2/18
50 kg drum	LGEP 2/50
180 kg drum	LGEP 2/180
Electro-mechanical lubricant dispensers	
TLMR 101 series 380 ml refill (incl. battery)	LGEP 2/MR380B
TLMR 201 series 380 ml refill	LGEP 2/MR380




## Technical data

Designation	LGEP 2/(pack size)		
DIN 51825 code	KP2G-20	Corrosion protection	
NLGI consistency class	2	Emcor: – standard ISO 11007	0-0
Thickener	Lithium	– water washout test	0-0
Colour	Light brown	– salt water test (100% seawater)	1-1 <sup>1)</sup>
Base oil type	Mineral	Water resistance	
Operating temperature range	-20 to +110 °C (-5 to +230 °F)	DIN 51 807/1, 3 hrs at 90 °C	1 max.
Dropping point DIN ISO 2176	>180 °C (>355 °F)	Oil separation	
Base oil viscosity:		DIN 51 817, 7 days at 40 °C, static, %	2-5
40 °C, mm <sup>2</sup> /s	200	Lubrication ability	
100 °C, mm <sup>2</sup> /s	16	R2F, running test B at 120 °C	Pass
Penetration DIN ISO 2137		Copper corrosion	
60 strokes, 10 <sup>-1</sup> mm	265-295	DIN 51 811	2 max. at 110 °C (230 °F)
100 000 strokes, 10 <sup>-1</sup> mm	+50 max. (325 max.)	EP performance	
Mechanical stability:		Wear scar DIN 51350/5, 1 400 N, mm	1,4 max
Roll stability, 50 hrs at 80 °C, 10 <sup>-1</sup> mm	+50 max.	4-ball test, welding load DIN 51350/4, N	2 800 min.
V2F test	'M'	Fretting corrosion	
		ASTM D4170 (mg)	5,7 <sup>1)</sup>

<sup>1)</sup> Typical value

## Lubrication management

Just as asset management takes maintenance to a higher level, a lubrication management approach allows lubrication to be seen from a wider point of view. This approach helps to effectively increase machine reliability at a lower overall cost.



[skf.com](http://skf.com) | [mapro.skf.com](http://mapro.skf.com) | [skf.com/lubrication](http://skf.com/lubrication)

© SKF is a registered trademark of the SKF Group.

© SKF Group 2017

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

PUB MP/P8 12045/2 EN · June 2017

Certain image(s) used under license from Shutterstock.com.