


X-ECOPUR H

*Thermoplastic polyurethane elastomer (TPU)
raw material base polyester (hydrolysis resistant)*

DIN: YAU ASTM: YAU

| Property | Unit | Value | Standard |
|--------------------------------|-------------------|------------|---|
| Standard color | – | Dark red |  |
| Durometer hardness* | Shore A | 97 ±1 | DIN ISO 7619 |
| Durometer hardness* | Shore D | 60 ±3 | DIN ISO 7619 |
| Density | g/cm ³ | 1,22 ±0,01 | DIN EN ISO 1183-1 |
| Tensile strength | MPa | ≥ 45 | DIN 53504 |
| Elongation at break | % | ≥ 350 | DIN 53504 |
| 100% modulus | MPa | ≥ 22 | DIN 53504 |
| Compression set: | | | |
| 70 °C / 24 h, 20% compression | % | ≤ 30 | DIN ISO 815 |
| 100 °C / 24 h, 20% compression | % | ≤ 35 | DIN ISO 815 |
| Tear strength | N/mm | 160 | DIN ISO 34-1 |
| Abrasion | mm ³ | 20 | DIN ISO 4649 |
| Minimum service temperature | °C | -20 | – |
| Maximum service temperature | °C | +110 | – |

IMPORTANT NOTE: The values shown above are only valid for material samples prepared for test purposes according to the stated standards.

* testing time is 3 s

© SKF and X-ECOPUR are registered trademarks of the SKF Group.

© SKF Group 2018

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

PUB SE/P8 12489/1 EN · July 2018

