


SKF Ecopaek

Polyaryletherketone (PEEK)

Property	Unit	Value	Standard
Standard color	–	Cream	
Durometer hardness	Shore D	87	ISO 868
Density	g/cm ³	1,30	DIN EN ISO 1183-1
Yield stress	MPa	100	ISO 527
Elongation at break	%	≥ 45	ISO 527
Tensile modulus	MPa	3 700	ISO 527
Impact resistance notched, charpy, 23 °C	kJ/m ²	7,0	ISO 179/1eA
Dimensional stability at high temperature HDT/A	°C	152	ISO R 75-f
Water absorption 24 h, 23 °C	%	0,07	ISO 62-1
Minimum service temperature	°C	–100	–
Maximum service temperature	°C	+260	–

IMPORTANT NOTE: The values shown above are only valid for material samples prepared for test purposes according to the stated standards.

© SKF is a registered trademark of the SKF Group.

© SKF Group 2014

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

PUB SE/P8 12478/1 EN · October 2014

