



Safety data sheet

Version: 01.01/AUS

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Trade name: LGMT 2

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended uses: Lubricant Lubricating grease

1.3. Details of the supplier of the safety data sheet

Distributor: SKF Australia Pty Ltd
17 - 21 Stamford Rd
3166 Oakleigh, VICTORIA
Australia
Tel: (03) 9269 0800
Fax: (03) 9269 0886
Email: SKF.australia@skf.com

1.4. Emergency telephone number

Emergency telephone comments: Poisons Information Centre: 13 11 26
(SKF Australia)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

GHS-classification

The product shall not be classified as hazardous according to GHS classification and labelling rules.

Most serious harmful effects:

May cause slight irritation to the skin and eyes. Degreases the skin. Long-term exposure may cause irritation and possible infection.

2.2. Label elements

The product shall not be classified as hazardous according to GHS classification and labelling rules.

2.3. Other hazards

None known.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Registration number	CAS/EC No.	Substance	w/w%	Note
.	84418-50-8	Naphthenic acids, zinc salts, basic	<1,2	.
.	282-762-6	.	.	.
.	Unknown	Non-hazardous mixture	>98,8	.
.	--	.	.	.

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:	Seek fresh air. Seek medical advice in case of persistent discomfort.
Ingestion:	Wash out mouth thoroughly and drink 1-2 glasses of water in small sips. Seek medical advice in case of discomfort.
Skin:	Remove contaminated clothing. Wash skin with soap and water. Seek medical advice in case of persistent discomfort.
Eyes	Flush with water (preferably using eye wash equipment) until irritation subsides. Seek medical advice if symptoms persist.
Other information:	When obtaining medical advice, show the safety data sheet or label.

4.2. Most important symptoms and effects, both acute and delayed

May cause slight irritation to the skin and eyes. Degreases the skin. Long-term exposure may cause irritation and possible infection.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptoms. No special immediate treatment required.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media Extinguish with powder, foam, carbon dioxide or water mist. Use water or water mist to cool non-ignited stock.

Unsuitable extinguishing media Do not use water stream, as it may spread the fire.

5.2. Special hazards arising from the substance or mixture

Not flammable, but combustible. Product decomposes in fire conditions or when heated to high temperatures, and inflammable and toxic gases may be released.

5.3. Advice for firefighters

Move containers from danger area if it can be done without risk. Avoid inhalation of vapour and flue gases – seek fresh air. Wear Self-Contained Breathing Apparatus (SCBA) with chemical resistant gloves. HazChem: 2Z (White "Z" on black background).

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel: Wear safety goggles if there is a risk of eye splash. Wear gloves.

For emergency responders: In addition to the above: Normal protective clothing is recommended.

6.2. Environmental precautions

Prevent spillage from entering drains and/or surface water.

6.3. Methods and material for containment and cleaning up

Contain and absorb spill with sand or other absorbent material and transfer to suitable waste containers. Wipe up minor spills with a cloth.

6.4. Reference to other sections

See section 8 for type of protective equipment. See section 13 for instructions on disposal.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

The product should be used under well-ventilated conditions and preferably under process ventilation. Running water and eye wash equipment should be available. Wash hands before breaks, before using restroom facilities, and at the end of work.

7.2. Conditions for safe storage, including any incompatibilities

The product should be stored safely, out of reach of children and away from food, animal feeding stuffs, medicines, etc. Do not store with the following: Strong oxidisers. Keep in tightly closed original packaging. Store in a dry, cool, well-ventilated area. Store at temperatures below 45°C.

7.3. Specific end use(s)

None.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Legal basis: WORKPLACE EXPOSURE STANDARDS FOR AIRBORNE CONTAMINANTS (DATE OF EFFECT: 18 April 2013)

	Contains no substances subject to reporting requirements.
8.2. Exposure controls	
Appropriate engineering controls:	Wear the personal protective equipment specified below.
Personal protective equipment, eye/face protection:	Wear safety goggles if there is a risk of eye splash.
Personal protective equipment, skin protection:	In the event of direct skin contact, wear protective gloves: Type of material and thickness: Nitrile rubber. >0,38 mm Penetration time: >8 hours.
Personal protective equipment, respiratory protection:	In case of risk of formation of spray mist, wear respiratory protective equipment with A/P2 filter.
Environmental exposure controls:	Ensure compliance with local regulations for emissions.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State:	Paste /Fat.
Colour:	Reddish brown
Odour:	No data
Odour threshold:	No data
pH (solution for use):	No data
pH (concentrate):	No data
Melting point/freezing point:	No data
Initial boiling point and boiling range:	No data
Flash point:	> 150 °C
Evaporation rate:	No data
Flammability (solid, gas):	No data
Upper/lower flammability limits:	No data
Upper/lower explosive limits:	No data
Vapour pressure:	No data
Vapour density:	No data
Relative density:	No data
Solubility:	Solubility in water: Insoluble
Partition coefficient n-octanol/water:	No data
Auto-ignition temperature:	No data
Decomposition temperature:	No data
Viscosity:	No data
Explosive properties:	No data
Oxidising properties:	No data

9.2. Other information

Bulk density: <1000 kg/m³ (25°C)

SECTION 10: Stability and reactivity

10.1. Reactivity

Reacts with the following: Strong oxidisers.

10.2. Chemical stability

The product is stable when used in accordance with the supplier's directions.

10.3. Possibility of hazardous reactions

None known.

10.4. Conditions to avoid

Avoid heating and contact with ignition sources.

10.5. Incompatible materials

Strong oxidisers.

10.6. Hazardous decomposition products

Product decomposes in fire conditions or when heated to high temperatures, and inflammable and toxic gases may be released.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity - oral: The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met. Ingestion of large quantities may cause discomfort.

LGMT 2: LD50 = 5126 mg/kg

84418-50-8: Rat: LD50 = 4920 mg/kg

Acute toxicity - dermal:	The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met. LGMT 2: LD50 = 4841 mg/kg
Acute toxicity - inhalation:	The product does not have to be classified. Test data are not available.
Skin corrosion/irritation:	The product does not have to be classified. Test data are not available. Degreases the skin. Long-term exposure may cause irritation and possible infection.
Serious eye damage/eye irritation:	The product does not have to be classified. Test data are not available. Temporary irritation.
Respiratory sensitisation or skin sensitisation:	The product does not have to be classified. Test data are not available.
Germ cell mutagenicity:	The product does not have to be classified. Test data are not available.
Carcinogenic properties:	The product does not have to be classified. Test data are not available.
Reproductive toxicity:	The product does not have to be classified. Test data are not available.
Single STOT exposure:	The product does not have to be classified. Test data are not available. Inhalation of vapours may cause irritation to the upper airways.
Repeated STOT exposure:	The product does not have to be classified. Test data are not available.
Aspiration hazard:	The product does not have to be classified. Test data are not available.
Other toxicological effects:	On warming/heating, the vapours emitted may cause irritation to the respiratory organs. May cause coughing and breathing difficulties.

SECTION 12: Ecological information

12.1. Toxicity

The product does not have to be classified. Test data are not available. The product contains small quantities of environmentally hazardous substances.

12.2. Persistence and degradability

Test data are not available. Not expected to be biodegradable.

12.3. Bioaccumulative potential

Test data are not available. No bioaccumulation expected.

12.4. Mobility in soil

Test data are not available. Not expected to be mobile in soil.

12.5. Results of PBT and vPvB assessment

No assessment has been made.

12.6. Other adverse effects

Oil products may cause soil and water pollution.

German water pollution classification (WGK): 1

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Avoid discharge to drain or surface water. Disposal should be in accordance with applicable regional, national and local laws and regulations. Local regulations may be more stringent than regional or national requirements.

Uncleansed packaging is to be disposed of via the local waste-removal scheme. Empty, cleansed packaging should be disposed of for recycling.

SECTION 14: Transport information

The product is not covered by the rules for transport of dangerous goods.

- 14.1. UN number -
 - 14.2. UN proper shipping name -
 - 14.3. Transport hazard class(es) -
 - 14.4. Packing group -
 - 14.5. Environmental hazards -
 - 14.6. Special precautions for user -
 - 14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code -
-

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Special provisions: None.

SECTION 16: Other information

Changes have been made in the following sections: 1, 3, 4, 7, 8, 9, 10, 11, 12, 13, 15, 16

Abbreviation explanations: PBT: Persistent, Bioaccumulative and Toxic
vPvB: Very Persistent and Very Bioaccumulative
STOT: Specific Target Organ Toxicity

Classification method: Calculation based on the hazards of the known components.

Training: A thorough knowledge of this safety data sheet should be a prerequisite condition.

Other information: This safety data sheet has been prepared for and applies to this product only. It is based on our current knowledge and the information that the supplier was able to provide about the product at the time of preparation. The safety data sheet complies with applicable law on preparation of safety data sheets in accordance with the WHS regulations.

Revision: 28-09-2017

Replaces: 26-03-2014
