

MATERIAL SAFETY DATA SHEET

Page : 1

Revision nr : 5

Date : 29/7/2003

Supersedes : 25/2/2003

R 606 T**R606T**

www.lisam.com

Supplier

SOGELUB N.V.

Rue de la Terre à Briques, 13

B-7522 Marquain Belgique-Belgie

Tel. +32 69 23 21 71

Antipoison Center - tel : + 32 (0)70 245 245

1. Identification of the product and the company

Identification of the product : Lubricant oil.
Trade name : R 606 T.
Company identification : See supplier.
Use : Industrial.

2. Information on ingredients

This product contains :

Substance name	Value(s)	CAS nr / EINECS nr / EC index	Symbol(s)	R-Phrase(s)
Aliphatic hydrocarbon	: < 50 %	064742-47-8 / 265-149-8 / -----	Xn	65-66

Other information : Preparation based on food grade refined oils, additives and PTFE.

3. Hazards identification

Main hazards : May cause lung damage if swallowed. Combustible material. May form flammable vapour-air mixture.

Symptoms relating to use

- Inhalation : Inhalation of vapours may cause respiratory irritation.
- Skin contact : Repeated or prolonged skin contact may cause irritation.
- Eye contact : Slight eye irritant.
- Ingestion : Not expected to present a significant ingestion hazard under anticipated conditions of normal use.

4. First aid measures

General information : Seek medical attention if ill effect develops.

First aid

- Inhalation : Assure fresh air breathing. Obtain medical attention if breathing difficulty persists.
- Skin contact : Wash skin thoroughly with mild soap and water.
- Eye contact : Rinse immediately with water. (15 min)
- Ingestion : Rinse mouth.

5. Fire - fighting measures

Extinguishing media

- Suitable : Carbon dioxide. Powder. Water fog.
- Not to be used : Do not use a heavy water jet.

Protection against fire : Use self-contained breathing apparatus when in close proximity to fire.

Special procedures : Do not breathe fumes from fires or vapours from thermal decomposition. Prevent fire-fighting water from entering environment.

6. Accidental release measures

Environmental precautions : Prevent entry to sewers and public waters.

After spillage and/or leakage : Area of spillage may be slippery. Dike for recovery or absorb with appropriate material. Use suitable disposal containers.

MATERIAL SAFETY DATA SHEET

Page : 2

Revision nr : 5

Date : 29/7/2003

Supersedes : 25/2/2003

R 606 T**R606T**

www.lisam.com

7. Handling and storage

- Storage : Avoid releasing into the environment. Store in dry, cool, well-ventilated area.
- Handling : Use only in well ventilated areas.
Keep at temperature not exceeding 65°C.
Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking as well as when leaving work.

8. Exposure controls / personal protection

- Personal protection
- Respiratory protection : No special respiratory protection equipment is recommended under normal conditions of use with adequate ventilation.
 - Hand protection : In case of repeated or prolonged contact wear gloves.
 - Skin protection : Remove soiled clothing promptly.
 - Eye protection : Goggles.
 - Ingestion : When using, do not eat, drink or smoke.
- Industrial hygiene : No special protection required where adequate ventilation is maintained.
- Exposure controls : Aliphatic hydrocarbon : TLV-TWA [mg/m3] : 1200
- TLV-TWA [mg/m3] : 5 (oil mist)
- TLV-STEL [mg/m3] : 10 (oil mist)

9. Physical and chemical properties

- Physical state : Oily liquid.
- Colour : White.
- Odour : Characteristic.
- pH value : Not applicable.
- Density : 843 kg/m3
- Vapour pressure [hPa] : < 1 (20°C, 1013hPa)
- Viscosity : 10 à 20 mm2/s (40°C)
- Solubility in water : Material insoluble in water.
- Flash point [°C] : > 70 (COC)
- Auto-ignition temperature [°C] : > 200
- Explosion limits - lower [%] : ca 0.5
- Explosion limits - upper [%] : ca 6

10. Stability and reactivity

- Hazardous decomposition products : None under normal conditions. When exposed to heat, may decompose liberating hazardous gases. (PTFE !)
- Materials to avoid : Oxidizing agent.
- Conditions to avoid : Overheating.

11. Toxicological information

- Acute toxicity : Not expected to be toxic.
- Ingestion : May cause lung damage if swallowed.
- Chronic toxicity
- Dermal : Repeated or prolonged skin contact may cause dermatitis and defatting.

MATERIAL SAFETY DATA SHEET	Page : 3
	Revision nr : 5
R 606 T	Date : 29/7/2003
	Supersedes : 25/2/2003
	R606T www.lisam.com

12. Ecological information

96 Hour-LC50 : No data available.
Information on elimination : No data available.
Mobility : Low mobility in the soil. Material insoluble in water.

13. Disposal considerations

Disposal : Dispose of this material and its container at hazardous or special waste collection point. Avoid releasing into the environment. Dispose of in a safe manner in accordance with local/national regulations.

14. Transport information

General information : Not regulated.

15. Regulatory information

Symbol(s) : None.
R Phrase(s) : R66 - Repeated exposure may cause skin dryness or cracking.
S Phrase(s) : S37 - Wear suitable gloves.

16. Other information

Official text of the R-phrases of § 2 : R65 - Harmful : may cause lung damage if swallowed.
R66 - Repeated exposure may cause skin dryness or cracking.
Further information : For professional use only.
Revision - See : *

The contents and format of this MSDS are in accordance with EEC Commission Directive 93/112/EEC.

DISCLAIMER OF LIABILITY The information in this MSDS was obtained from sources which we believe are reliable. However, the information is provided without any warranty, express or implied, regarding its correctness. The conditions or methods of handling, storage, use or disposal of the product are beyond our control and may be beyond our knowledge. For this and other reasons, we do not assume responsibility and expressly disclaim liability for loss, damage or expense arising out of or in any way connected with the handling, storage, use or disposal of the product. This MSDS was prepared and is to be used only for this product. If the product is used as a component in another product, this MSDS information may not be applicable.

End of document