



SAFETY DATA SHEET

Material safety data sheet

LGEV 2

Last changed: 2006-03-27

1. IDENTIFICATION OF PRODUCT AND COMPANY

TRADE NAME LGEV 2
APPLICATION High viscosity with solid lubricants.

Supplier
Company SKF Maintenance Products
Address Postbus 1008
Postal code NL-3430 BA Nieuwegein
Country The Netherlands
Telephone +31 30 6307200
Fax +31 30 6307205
Contact person Sébastien David
e-mail sebastien.david@skf.com

2. COMPOSITION/INFORMATION ON INGREDIENTS

No	Ingredient name	EC No.	CAS No.	Conc. (wt %)	Classification
1	Dialkylpolsulfide derivate			1 - 2,5 %	R53
2	Amines, C11-14-branched alkyl, monohexyl and dihexyl phosphates	279-632-6	80939-62-4	< 1 %	Xi,N,R36/38 - R51/53
Legend: T+ =Very toxic, T=Toxic, C=Corrosive, Xn=Harmful, Xi=Irritant, E=Explosive, O=Oxidising, F+ =Extremely flammable, F=Highly flammable, N=Dangerous for the environment, Carc. = Carcinogenic, Mut. = Mutagenic, Repr. = Reproductive					

INGREDIENT COMMENTS

The complete text of the R-phrases mentioned in section 2 is stated in section 16.

3. HAZARDS IDENTIFICATION

HEALTH

May be irritating to eyes.
Prolonged or frequently recurrent contact will degrease the skin and may cause skin irritation.

FIRE AND EXPLOSION

Not flammable, but combustible.

ENVIRONMENT

Oil products may cause ground and water pollutants.

4. FIRST AID MEASURES

INHALATION

Remove victim immediately from source of exposure. Provide rest, warmth and fresh air. Seek medical advice if symptoms develop.

SKIN CONTACT

Immediately flush contaminated skin with soap or mild detergent and water. Immediately remove soaked clothing and flush the skin with water. Use appropriate hand lotion to prevent degreasing and cracking of skin. Seek medical advice if irritation persists.

EYE CONTACT

Immediately flush eyes with plenty of water while holding eye lids open. Remove any contact lenses and continue rinsing with water for at least 15 minutes (keep the eyelids open). Seek medical advice if irritation persists.

INGESTION

DO NOT INDUCE VOMITING! If vomiting occurs, keep head low so that stomach contents do not enter lungs. Thoroughly rinse the mouth with water. Drink a few glasses of water or milk. Seek medical advice.



Last changed: 2006-03-27

5. FIRE-FIGHTING MEASURES

EXTINGUISHING MEDIA

Extinguishing agent: carbon dioxide, powder, foam, water spray or water mist.

IMPROPER EXTINGUISHING MEDIA

Do not use a direct water stream which may spread the fire.

EXTINGUISHING METHODS

Remove containers from fire area if this can be done without risk. Use water to cool exposed containers. If possible, fight the fire from a protected location.

FIRE AND EXPLOSION HAZARDS

Not flammable, but combustible. Carbon monoxide and hydrocarbons are released under fire conditions.

PROTECTIVE EQUIPMENT FOR FIRE FIGHTERS

General: Evacuate all personnel, use protective equipment for fire fighting. Use a portable breathing apparatus when the product is involved in a fire.

6. ACCIDENTAL RELEASE MEASURES

PERSONAL PRECAUTIONS

Provide good ventilation.
Avoid contact with the skin, eyes and airways.
Wear necessary protective equipment. Keep the emission away from sources of ignition.

ENVIRONMENTAL PRECAUTIONS

Must not be released into the sewage system, drinking water supply or ground.

METHODS FOR CLEANING UP

Dry, scrape or absorb the product with inert material and place it in a refuse container. Collect and dispose of materials in closed and labelled containers at an approved disposal or waste collection facility. Clean with soap and water or detergent. Flush clean with plenty of water. Be aware of the risk of slippery surfaces.

7. HANDLING AND STORAGE

HANDLING ADVICE

Provide good ventilation. Avoid contact with the skin and eyes. Wear necessary protective equipment. Keep away from sources of ignition.

STORAGE

Keep in original container. Store at room temperature. Keep away from sources of ignition. Avoid contact with oxidising substances and strong acids.

8. EXPOSURE CONTROL/PERSONAL PROTECTION

EXPOSURE CONTROL

Provide good ventilation. Wash the skin at the end of each work shift and before eating, smoking and using restroom facilities. Eye wash facilities and safety shower must be available when handling this product.

RESPIRATORY PROTECTION

Respiratory protective equipment is usually not necessary. In case of insufficient ventilation, wear respiratory protective equipment with A/P2 filter.

EYE PROTECTION

Wear approved safety goggles if there is a risk of eye splash.

HAND PROTECTION

Protective gloves (nitrile rubber, Viton®).

PROTECTIVE CLOTHING

Wear suitable protective clothing.



SAFETY DATA SHEET

Material safety data sheet

LGEV 2

Last changed: 2006-03-27

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical State Paste.
Colour Grey.
Odour Mineral oil.
Water solubility Insoluble in water.

Physical and chemical parameters

Parameter	Value / Unit	Method	Note
Flash point	> 200 °C	ISO 2592	
Density	0,94 g/cm ³	DIN 51 757 / 20 °C	
Dropping point	~ 180 °C / IP 396 s, Wirkstoffha		

10. STABILITY AND REACTIVITY

STABILITY

Stable under recommended storage and handling conditions.

CONDITIONS TO AVOID

Avoid heat, sparks and naked flames.

MATERIALS TO AVOID

Avoid contact with oxidising substances and strong acids

11. TOXICOLOGICAL INFORMATION

INHALATION

On warming/heating, the vapours emitted may cause irritation to the respiratory organs. May cause coughing and breathing difficulties.

SKIN CONTACT

Prolonged or frequently recurrent contact will degrease the skin and may cause skin irritation.

EYE CONTACT

May cause moderate irritation/smartering.

INGESTION

May cause irritation of the mucous membranes, nausea and vomiting.

12. ECOLOGICAL INFORMATION

MOBILITY

Insoluble in water. The product floats on water.

OTHER EFFECTS

Oil products may cause ground and water pollutants.

CONCLUSION

Must not be released into the sewage system, drinking water supply or ground.

OTHER INFORMATION

German water pollution classification (WGK): 2



SAFETY DATA SHEET

Material safety data sheet

LGEV 2

Last changed: 2006-03-27

13. DISPOSAL CONSIDERATIONS

GENERAL REGULATIONS

Treat as hazardous waste. Collect and dispose of materials in closed and labelled containers at an approved disposal or waste collection facility. Empty packages must be handled in an environmentally safe manner in accordance with applicable laws and regulations.

CATEGORY OF WASTE

The EWC code is a suggestion only; the end user will select a suitable EWC code. 12 01 12* spent waxes and fats.

14. TRANSPORT INFORMATION

Classified as Dangerous Goods:

Yes

No

N/A

OTHER INFORMATION

Not classified as dangerous goods.

15. REGULATORY INFORMATION

EC-Label

Yes

No

N/A

COMPOSITION

Dialkylpolsulfide derivat (1 - 2,5 %), Amines, C11-14-branched alkyl, monohexyl and dihexyl phosphates (< 1 %)

S-PHRASES

S24/25 Avoid contact with skin and eyes.

S37 Wear suitable gloves.

REFERENCES

Directive 1999/45/EC.

Annex I to Directive 67/548/EEC on Classification and Labelling of Dangerous Substances.

Directive 2001/58/EC (91/155/EEC).

European Waste Catalogue (EWC 2002).

Occupational exposure limits (EH40/2006)

Transport of dangerous goods: ADR, RID, IMDG and IATA.

16. OTHER INFORMATION

LIST OF RELEVANT R-PHRASES

Nr.	R-Phrase text
R36/38	Irritating to eyes and skin.
R51/53	Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R53	May cause long-term adverse effects in the aquatic environment.

ISSUED:

27/03/2006