

Low temperature chassis grease

LGLS 0

SKF LGLS 0 is a semi-fluid chassis grease that has been developed to be used via lubrication systems under low to medium temperatures. Its anhydrous calcium thickener, combined with a high base oil viscosity, offers excellent water resistance and stickiness to surfaces as well as very good anti-wear properties.

- Excellent pumpability at low to medium temperatures
- Excellent water resistance and corrosion protection
- Excellent anti-wear properties
- Excellent adhesion to surfaces

Typical applications

- Construction equipment
- Heavy duty off-road applications such as excavators, wheel loaders, etc
- Forestry and agricultural equipment such as forwarders and harvesters
- Collector trucks
- Joints
- Slow plain and rolling bearings



Available pack sizes

Packsizes	Designation
18 kg pail	LGLS 0/18
50 kg drum	LGLS 0/50
180 kg drum	LGLS 0/180




Technical data

Designation	LGLS 0/(pack size)		
DIN 51825 code	KPOG-40	Penetration DIN ISO 2137 60 strokes, 10 ⁻¹ mm	355–385
NLGI consistency class	0	Corrosion protection SKF Emcor standard ISO 11007	0-0
Thickener	Anhydrous calcium	Flow pressure at -40 °C	<1 400 mbar
Colour	Red	EP performance 4-ball test, welding load DIN 51350/4	3 200 N
Base oil type	Mineral oil & polymers		
Operating temperature range	-40 to +100 °C (-40 to +212 °F)		
Dropping point IP 396	>120 °C (>248 °F)		
Base oil viscosity 40 °C, mm ² /s	1 370		
100 °C, mm ² /s	96		

Lubrication management

Just as asset management takes maintenance to a higher level, a lubrication management approach allows lubrication to be seen from a wider point of view. This approach helps to effectively increase machine reliability at a lower overall cost.



skf.com | mapro.skf.com | skf.com/lubrication

© SKF is a registered trademark of the SKF Group.

© SKF Group 2018

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

PUB MP/P8 15757/2 EN · September 2018

Certain image(s) used under license from Shutterstock.com.