


Machined seals

Profiles overview




Piston seals




Thanks to our innovative manufacturing process we are able to produce virtually any profile in any dimension and material.

Wipers




Rod seals




Indicated materials (colors) are examples, profiles are available in a wide range of standard and non-standard materials.


Rotary seals



Guide rings



Back-up rings




Materials overview

	Material colour	Shore A/D hardness	Operating temperature, °F		Mineral oil based resistance		HFA-E water +oil emuls. resistance		Water resistance	
			min.	max.	RT	140 °F	RT	140 °F	RT	140 °F
Elastomers, polyurethanes										
ECOPUR	Polyurethane (TPU)	■ 95/48	-22	230	+	+	0	-	+	-
ECOPUR LD	Cast polyurethane (CPU)	■ 95/48	-31	230	+	+	0	-	+	-
G-ECOPUR	Cast polyurethane (CPU)	■ 95/47	-22	230	+	+	+	0	+	0
H-ECOPUR	Polyurethane (TPU)	■ 95/48	-4	230	+	+	+	+	+	+
S-ECOPUR	Polyurethane (TPU)	■ 95/48	-4	230	+	+	+	+	+	+
T-ECOPUR	Polyurethane (TPU)	■ 95/48	-58	230	+	+	0	-	+	-
X-ECOPUR	Hard grade polyurethane (TPU)	■ 97/57	-22	230	+	+	0	-	+	-
X-ECOPUR H	Hard grade polyurethane (TPU)	■ 97/60	-4	230	+	+	+	+	+	+
X-ECOPUR S	Hard grade polyurethane (TPU)	■ 96/58	-4	230	+	+	+	+	+	+
Elastomers, rubber										
SKF Ecoflas	Tetrafluoroethylene propylene rubber (TFE/P)	■ 83/-	14	392	+	+	+	+	+	+
SKF Ecorubber-H	Hydrogenated NBR (H-NBR)	■ 85/-	-13	302	+	+	+	+	+	+
SKF Ecorubber-1	Acrylonitrile butadiene rubber (NBR)	■ 85/-	-22	212	+	+	+	+	+	+
SKF Ecorubber-2	Fluorocarbonate rubber (FKM)	■ 85/-	-4	392	+	+	+	0	+	+
SKF Ecorubber-3	Ethylene propylene diene rubber (EPDM)	■ 85/-	-58	202	-	-	-	-	+	+
SKF Ecosil	Silicone rubber (MVQ)	■ 85/-	-76	392	+/0	+/0	0	0	+	+
Thermoplastics										
SKF Ecoflon 1	Polytetrafluoroethylene (PTFE)	■ -/57	-328	500	+	+	+	+	+	+
SKF Ecoflon 2	Polytetrafluoroethylene +15% glass +5% MoS ₂	■ -/62	-328	500	+	+	+	+	+	+
SKF Ecoflon 3	Polytetrafluoroethylene +40% bronze	■ -/65	-328	500	+	+	+	+	+	+
SKF Ecoflon 4	Polytetrafluoroethylene +25% carbon	■ -/65	-328	500	+	+	+	+	+	+
SKF Ecomid	Polyamide (PA)	■ -/77	-40	230	+	+	+	+	0	0
SKF Ecopaek	Polyaryletherketone (PEEK)	■ -/87	-148	500	+	+	+	+	+	+
SKF Ecotal	Polyacetal (POM)	■ -/8	-58	212	+	+	+	+	+	+
SKF Ecowear	Ultra-High Molecular Weight Polyethylene (UHMWPE)	■ -/-	-328	194	+	+	+	+	+	+

+ Suitable
 0 Unknown data or limited resistance
 - Not recommended
 RT Room temperature (68 °F)



Open to see the full range of machined seals, wipers, guide rings and back-up rings.



The Power of Knowledge Engineering

Combining products, people, and application-specific knowledge, SKF delivers innovative solutions to equipment manufacturers and production facilities in every major industry worldwide. Having expertise in multiple competence areas supports SKF Life Cycle Management, a proven approach to improving equipment reliability, optimizing operational and energy efficiency and reducing total cost of ownership.

These competence areas include bearings and units, seals, lubrication systems, mechatronics, and a wide range of services, from 3-D computer modelling to cloud-based condition monitoring and asset management services.

SKF's global footprint provides SKF customers with uniform quality standards and worldwide product availability. Our local presence provides direct access to the experience, knowledge and ingenuity of SKF people.

© SKF, ECOPUR, G-ECOPUR, H-ECOPUR, S-ECOPUR, T-ECOPUR and X-ECOPUR are registered trademarks of the SKF Group.

© SKF Group 2015

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

The data in this publication may differ from that shown in earlier publications because of redesign, technological developments or revised methods of calculation. SKF reserves the right to make continuing improvements to SKF products without prior notice with respect to materials, design and manufacturing methods, as well as changes necessitated by technological developments.

PUB SE/P2 11302/2 EN-US

(10M/AN 1/2015)

Version 1/2015

Printed in U.S.A.

Certain image(s) used under license from Shutterstock.com

