



# Reducing gas flaring to cut CO<sub>2</sub> emissions



## Environmental benefits

- Reduced CO<sub>2</sub> emissions
- Reduced flaring of sour gas
- Reduced risk of toxic sour gas emissions
- Reduced risk of mercury emissions



**Using SKF sour gas compressor bearings in a vapor recovery unit could cut CO<sub>2</sub> emissions by as much as 24 000 tonnes over 12 years.**

## SKF sour gas compressor bearings slash CO<sub>2</sub> and SO<sub>2</sub> emissions from gas flaring

Every year, the oil and gas industry “flares” – that is, burns or vents – an estimated 150 billion cubic meters (5.3 trillion cubic feet) of waste gases\*. That’s equivalent to 25% of annual US natural gas consumption or 30% of the EU’s. Along with SO<sub>2</sub> that causes acid rain, gas flaring emits about 400 million tons of CO<sub>2</sub>, or about 1.2% of all annual global CO<sub>2</sub> emissions.

Much of this flared gas can be captured by vapor recovery units (VRUs) and then be used or re-injected. But doing so reliably is a serious challenge, as the harsh process gases can cause VRU compressor bearings to wear out and fail in six months or less. When bearing failures cause unplanned compressor downtime, gas recovery stops and emergency gas flaring restarts.

By significantly extending compressor service life, SKF sour gas compressor bearings can cut the frequency of gas

flaring dramatically. Proven to withstand exposure to sour gas and other process gases, SKF sour gas compressor bearings can deliver 6-10 times the service life of conventional bearings. Over a typical, 12-year compressor lifecycle, this extension of bearing uptime would enable a savings of 8 000 – 24 000 tonnes of CO<sub>2</sub> emissions, depending on compressor capacity.



SKF BeyondZero solutions can help reduce CO<sub>2</sub> emissions, preserve limited resources and protect the environment from the use and spread of toxic substances. For more details, including documentation of reduced environmental impact, visit [www.beyondzero.com](http://www.beyondzero.com)

\*Source: The World Bank, Global Gas Flaring Reduction Partnership, 2013: <http://go.worldbank.org/425V06DY50>



# SKF sour gas compressor bearings

## Operational benefits

- **6-10 times longer service life than conventional bearings**
- **Increased compressor reliability and productivity**
- **Small footprint and simplified compressor installation**
- **Highly reliable and low CAPEX VRU installations**
- **Reduced compressor operating costs**
- **Reduced energy requirement vs. hydrodynamic bearings**

## Operational features

- **Super-tough, high-nitrogen stainless steel rings**
- **Glass fiber-reinforced polymeric PEEK cages**
- **Silicon nitride ceramic balls and rollers**

## References and design conditions

- **First sour gas pilot in 2004**
- **Used in SSC NACE/ISO, region 3 inlet conditions**
- **40 mol% H<sub>2</sub>S and 35 mol% CO<sub>2</sub> combined**
- **100 mol% H<sub>2</sub>S and CO<sub>2</sub> combined**
- **Hydrogen-rich gases**

## The screw compressor challenge

Across gas plants, offshore platforms, oil field separators and refineries, the use of oil-flooded screw compressors for vapor recovery units (VRU) is on the rise. Their relative low cost, small footprint and performance flexibility make them a good fit for the application. Screw compressor reliability, however, is a challenge – a particularly costly one when the VRU is located near a well in a remote location.

The problem? Sour gas (H<sub>2</sub>S), condensing water and acid gases in the compressor are in direct contact with the bearings and may attack them very aggressively under fluctuating process conditions. Conventional bearings offer little resistance to the sour gas, so bearing raceways and rolling elements will eventually start to flake, then undergo rapid bearing failure.

## The SKF sour gas solution

Developed as a robust alternative to conventional steel bearings with brass cages, SKF sour gas compressor bearings feature several high performance materials. These include high-nitrogen stainless steel rings, glass fiber-reinforced polymeric PEEK cages, plus silicon nitride ceramic balls and rollers.

This combination of materials enables excellent resistance to sulfide and hydrogen stress cracking, poor lubrication, corrosion, and electrical arcing from variable frequency drives. The ultimate result: SKF sour gas compressor bearings offer 6-10 times the service life of conventional bearings in oil-flooded screw compressors. Along with significant reductions in CO<sub>2</sub> emissions, this SKF solution is enabling sharp reductions in compressor maintenance demands and operating costs.



© SKF is a registered trademark of the SKF Group.

™ BeyondZero is a trademark of the SKF Group.

© SKF Group 2014

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein. Any statements in this publication concerning environmental impacts, as well as cost savings and revenue increases, are based on results experienced by SKF customers and/or based on internal calculations by SKF personnel and do not constitute a guarantee that any future results will be the same.

PUB 75/S7 14625 EN · May 2014

Certain image(s) used under license from Shutterstock.com.

