


DS35-P



Ordering dimensions in **blue**

Surface roughness R_{tmax} R_a

Sliding surface $\leq 2,5 \mu m$ $0,05-0,3 \mu m$

Bottom of groove $\leq 6,3 \mu m$ $\leq 1,6 \mu m$

Groove face $\leq 15 \mu m$ $\leq 3 \mu m$

Bearing area: 50–95% and a cutting depth of 0,5 R_z based on $C_{ref} = 0\%$

Standard dimensions

d f8 over	D H10 incl.	L + 0,2	R_{max}	c	Maximal radial extrusion gap				
					s^1)				
					20 bar	100 bar	200 bar	400 bar	
mm					mm				
5	10	d + 5	4,0	0,4	2,0	0,33	0,18	0,10	0,05
10	25	d + 6	4,5	0,4	3,0	0,33	0,18	0,10	0,05
25	50	d + 8	5,5	0,4	3,5	0,33	0,18	0,10	0,05
50	100	d + 10	6,5	0,4	4,0	0,37	0,23	0,15	0,10
100	150	d + 15	9,5	0,4	5,0	0,46	0,33	0,25	0,18
150	200	d + 20	12,5	0,4	6,0	0,54	0,38	0,33	0,25

¹⁾ Extrusion gap values shown above are valid for a temperature of 70 °C, higher temperatures require lower values.

Ordering example

Profile
d x D x L [mm]
Sealing material

Rod Seal DS35-P
120 x 135 x 9,5
ECOPUR DD

Operating parameters

Material Seal	Temperature		Speed ^{1) 2)}	Pressure ³⁾
	from	to	max	max
–	°C		m/s	bar (MPa)
■ ECOPUR DD	–30	+100	0,4	400 (40)

IMPORTANT NOTE: The stated operating conditions represent general indications. It is recommended not to use all maximum values simultaneously.

¹⁾ Surface speed limit values are valid only in the presence of a lubrication film.

²⁾ Rotary applications max. 0,2 m/s

³⁾ Pressure ratings depend on the size of the extrusion gap.