


A01-B



Ordering dimensions in **blue**

Surface roughness	R_{tmax}	R_a
Sliding surface	$\leq 2,5 \mu m$	$0,05-0,3 \mu m$
Bottom of groove	$\leq 6,3 \mu m$	$\leq 1,6 \mu m$
Groove face	$\leq 15 \mu m$	$\leq 3 \mu m$

Bearing area: 50–95% and a cutting depth of $0,5 R_z$ based on $C_{ref} = 0\%$

Standard dimensions

d	f8	D	D_1	L	L_1	R_{max}	R	H
over	incl.	H11	H11	+0,2				
mm								
5	100	$d + 8$	$d + 6$	4	1	0,4	$\leq 0,4$	7,6
100	150	$d + 12$	$d + 9$	5,5	1,5	0,4	$\leq 0,4$	10,45
150	600	$d + 15$	$d + 11$	6,5	2	0,4	$\leq 0,4$	12,35

Ordering example

Profile
 $d \times D/D_1 \times L/L_1$ [mm]
Sealing material

Wiper A01-B
50 x 58/56 x 4/1
ECOPUR

Operating parameters

Material Seal	Temperature		Speed ¹⁾
	from	to	max
–	°C		m/s
■ ECOPUR	–30		
■ ECOPUR LD	–35		
■ G-ECOPUR	–30		
■ G-ECOPUR 54D	–30		
■ H-ECOPUR	–20	+110	
■ S-ECOPUR			
■ T-ECOPUR	–50		
■ X-ECOPUR	–30		4
■ X-ECOPUR H	–20		
■ X-ECOPUR S			
■ SKF Ecoflas	–10	+200	
■ SKF Ecorubber-H	–25	+150	
■ SKF Ecorubber-1	–30	+100	
■ SKF Ecorubber-2	–20	+200	
■ SKF Ecorubber-3	–50	+150	

IMPORTANT NOTE: The stated operating conditions represent general indications. It is recommended not to use all maximum values simultaneously.

¹⁾ Surface speed limit values are valid only in the presence of a lubrication film.