

# Safety data sheet

Revision: 10-03-2018  
 Replaces: 10-04-2015  
 Version: 02.01/GBR

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1. Product identifier

Trade name: LGGB 2

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended uses: Lubricant Lubricating grease

### 1.3. Details of the supplier of the safety data sheet

Supplier: SKF MAINTENANCE PRODUCTS  
 Postbus 1008  
 NL-3430 BA Nieuwegein  
 The Netherlands  
 Tel: +31 30 6307200  
 Email: sebastien.david@skf.com  
 WWW: www.skf.com

### 1.4. Emergency telephone number

0870 600 6266 (UK only) Only available to health professionals.

## SECTION 2: Hazards identification

### 2.1. Classification of the substance or mixture

CLP-classification (Regulation  
 (EC) No 1272/2008):

The product shall not be classified as hazardous according to the classification and labelling rules for substances and mixtures.

Most serious harmful effects:

May cause slight irritation to the skin and eyes.

### 2.2. Label elements

The product shall not be classified as hazardous according to the classification and labelling rules for substances and mixtures.

### 2.3. Other hazards

Assessment to determine PBT and vPvB has not been made.

## SECTION 3: Composition/information on ingredients

### 3.2. Mixtures

Registration number	CAS/EC Number	Substance	CLP-classification (Regulation (EC) No 1272/2008)	w/w%	Note
		Contains no substances subject to reporting requirements.			

Please see section 16 for the full text of H-phrases.

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

Inhalation:	Seek fresh air. Seek medical advice in case of persistent discomfort.
Ingestion:	Wash out mouth thoroughly and drink 1-2 glasses of water in small sips. Seek medical advice in case of discomfort.
Skin:	Remove contaminated clothing. Wash skin with soap and water. Seek medical advice in case of persistent discomfort.
Eyes:	Flush with water (preferably using eye wash equipment) until irritation subsides. Seek medical advice if symptoms persist.
Other information:	When obtaining medical advice, show the safety data sheet or label.

#### **4.2. Most important symptoms and effects, both acute and delayed**

May cause slight irritation to the skin and eyes.

#### **4.3. Indication of any immediate medical attention and special treatment needed**

Treat symptoms. No special immediate treatment required.

### **SECTION 5: Firefighting measures**

#### **5.1. Extinguishing media**

Suitable extinguishing media      Extinguish with powder, foam, carbon dioxide or water mist. Use water or water mist to cool non-ignited stock.

Unsuitable extinguishing media      Do not use water stream, as it may spread the fire.

#### **5.2. Special hazards arising from the substance or mixture**

Not flammable, but combustible. Product decomposes in fire conditions or when heated to high temperatures, and inflammable and toxic gases may be released.

#### **5.3. Advice for firefighters**

Move containers from danger area if it can be done without risk. Avoid inhalation of vapour and flue gases – seek fresh air. Wear Self-Contained Breathing Apparatus (SCBA) with chemical resistant gloves.

### **SECTION 6: Accidental release measures**

#### **6.1. Personal precautions, protective equipment and emergency procedures**

For non-emergency personnel:      Wear safety goggles if there is a risk of eye splash. Wear gloves.

For emergency responders:          In addition to the above: Normal protective clothing equivalent to EN 469 is recommended.

#### **6.2. Environmental precautions**

Prevent spillage from entering drains and/or surface water.

#### **6.3. Methods and material for containment and cleaning up**

Contain and absorb spill with sand or other absorbent material and transfer to suitable waste containers. Wipe up minor spills with a cloth. Rinse with water.

#### **6.4. Reference to other sections**

See section 8 for type of protective equipment. See section 13 for instructions on disposal.

### **SECTION 7: Handling and storage**

#### **7.1. Precautions for safe handling**

The product should be used under well-ventilated conditions and preferably under process ventilation. Running water and eye wash equipment should be available. Wash hands before breaks, before using restroom facilities, and at the end of work.

#### **7.2. Conditions for safe storage, including any incompatibilities**

The product should be stored safely, out of reach of children and away from food, animal feeding stuffs, medicines, etc. Do not store with the following: Strong oxidisers/ Strong acids/ Strong alkalis.

#### **7.3. Specific end use(s)**

None.

### **SECTION 8: Exposure controls/personal protection**

#### **8.1. Control parameters**

Legal basis:                                EH40/2005 Workplace exposure limits. Last amended December 2011.

Contains no substances subject to reporting requirements.

#### **8.2. Exposure controls**

Appropriate engineering controls:	Wear the personal protective equipment specified below.
Personal protective equipment, eye/face protection:	Wear safety goggles if there is a risk of eye splash. Eye protection must conform to EN 166.
Personal protective equipment, skin protection:	Wear gloves. Type of material and thickness: Nitrile rubber. $\geq 0,038\text{mm}$ Penetration time: $>8$ hours. Gloves must conform to EN 374.
Personal protective equipment, respiratory protection:	Not required.
Environmental exposure controls:	Ensure compliance with local regulations for emissions.

---

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

State:	Paste /Fat.
Colour:	Light brown
Odour:	Characteristic
Odour threshold:	No data
pH (solution for use):	No data
pH (concentrate):	No data
Melting point/freezing point:	No data
Initial boiling point and boiling range:	No data
Flash point:	No data
Evaporation rate:	No data
Flammability (solid, gas):	No data
Upper/lower flammability limits:	No data
Upper/lower explosive limits:	No data
Vapour pressure:	No data
Vapour density:	No data
Relative density:	0,87 (25 °C)
Solubility:	Insoluble in the following: Water.
Partition coefficient n-octanol/water:	No data
Auto-ignition temperature:	No data
Decomposition temperature:	No data
Viscosity:	No data
Explosive properties:	No data
Oxidising properties:	No data

### 9.2. Other information

NLGI: 2

---

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

Reacts with the following: Strong oxidisers/ Strong acids/ Strong alkalis.

### 10.2. Chemical stability

The product is stable when used in accordance with the supplier's directions.

### 10.3. Possibility of hazardous reactions

None known.

### 10.4. Conditions to avoid

Avoid heating and contact with ignition sources.

### 10.5. Incompatible materials

Strong oxidisers/ Strong acids/ Strong alkalis.

### 10.6. Hazardous decomposition products

Product decomposes in fire conditions or when heated to high temperatures, and inflammable and toxic gases may be released.

---

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

Acute toxicity - oral: The product does not have to be classified. Test data are not available. Ingestion of large quantities may cause discomfort.

Acute toxicity - dermal: The product does not have to be classified. Test data are not available.

Acute toxicity - inhalation:	The product does not have to be classified. Test data are not available.
Skin corrosion/irritation:	The product does not have to be classified. Test data are not available. Degreases the skin. Long-term exposure may cause irritation and possible infection.
Serious eye damage/eye irritation:	The product does not have to be classified. Test data are not available. Temporary irritation.
Respiratory sensitisation or skin sensitisation:	The product does not have to be classified. Test data are not available.
Germ cell mutagenicity:	The product does not have to be classified. Test data are not available.
Carcinogenic properties:	The product does not have to be classified. Test data are not available.
Reproductive toxicity:	The product does not have to be classified. Test data are not available.
Single STOT exposure:	The product does not have to be classified. Test data are not available.
Repeated STOT exposure:	The product does not have to be classified. Test data are not available.
Aspiration hazard:	The product does not have to be classified. Test data are not available.
Other toxicological effects:	On warming/heating, the vapours emitted may cause irritation to the respiratory organs. May cause coughing and breathing difficulties.

---

## SECTION 12: Ecological information

### 12.1. Toxicity

The product does not have to be classified. Test data are not available.

### 12.2. Persistence and degradability

Test data are not available.

### 12.3. Bioaccumulative potential

Test data are not available.

### 12.4. Mobility in soil

Test data are not available.

### 12.5. Results of PBT and vPvB assessment

No assessment has been made.

### 12.6. Other adverse effects

Forms an oil film on water surfaces that may harm aquatic organisms and may disturb the transport of oxygen at the air-water interface.

German water pollution classification (WGK): 1

---

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

Avoid discharge to drain or surface water. If this product as supplied becomes a waste, it does not meet the criteria of a hazardous waste (Dir. 2008/98/EU). Disposal should be in accordance with applicable regional, national and local laws and regulations. Local regulations may be more stringent than regional or national requirements.

EWC code: Depends on line of business and use, for instance 12 01 99 wastes not otherwise specified

Absorbent/cloth contaminated with the product: EWC code: 15 02 03 Absorbents, filter materials, wiping cloths and protective clothing other than those mentioned in 15 02 02.

Uncleansed packaging is to be disposed of via the local waste-removal scheme. Empty, cleansed packaging should be disposed of for recycling.

**SECTION 14: Transport information**

The product is not covered by the rules for transport of dangerous goods.

- 14.1. UN number -  
14.2. UN proper shipping name -  
14.3. Transport hazard class(es) -  
14.4. Packing group -  
14.5. Environmental hazards -  
14.6. Special precautions for user -  
14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code -

---

**SECTION 15: Regulatory information****15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

Special provisions: None.

**15.2. Chemical safety assessment**

Chemical safety assessment has not been performed.

---

**SECTION 16: Other information**

Changes have been made in the following sections: 2,3,8,13,16

Abbreviation explanations: PBT: Persistent, Bioaccumulative and Toxic  
vPvB: Very Persistent and Very Bioaccumulative  
STOT: Specific Target Organ Toxicity

Classification method: Calculation based on the hazards of the known components.

H-phrases: No H-phrases.

Training: A thorough knowledge of this safety data sheet should be a prerequisite condition.

Other information: This safety data sheet has been prepared for and applies to this product only. It is based on our current knowledge and the information that the supplier was able to provide about the product at the time of preparation. The safety data sheet complies with applicable law on preparation of safety data sheets in accordance with 1907/2006/EC (REACH) as subsequently changed.

---