


R01-AF



Ordering dimensions in **blue**

Surface roughness	R_{tmax}	R_a
Sliding surface	$\leq 2,5 \mu m$	$0,1-0,5 \mu m$
Bottom of groove	$\leq 6,3 \mu m$	$\leq 1,6 \mu m$
Groove face	$\leq 15 \mu m$	$\leq 3 \mu m$

Hardness: Min 45 HRC (55 HRC recommended), hardened depth > 0,3 mm.
Bearing area: 50-95% and a cutting depth of 0,5 R_z based on $C_{ref} = 0\%$

Standard dimensions

d		d		D	L	c	R_{max}
h11		h11		H8	-0,2		
Rotating application		Pivoting application					
over	incl.	over	incl.				
mm							
5	80	5	40	D + 15	7	1,2	0,4
80	140	40	70	D + 20	8	1,5	0,4
140	240	70	120	D + 20	10	1,5	0,4
240	480	120	240	D + 30	12	1,8	0,8
480	2 240	240	1 120	D + 40	15	1,8	0,8
2 240	3 200	1 120	1 600	D + 50	25	3,3	0,8
3 200		1 600		D + 60	30	3,3	0,8

Ordering example

Profile
d x D x L [mm]
Sealing material / Spring

Rotary seal R01-AF
100 x 120 x 8
ECOPUR / 1.4310

Operating parameters

Material Seal	Spring	Temperature		Speed ^{1) 2) 3)}	Pressure
		from	to	max	max
		°C		m/s	bar (MPa)
■ ECOPUR	1.4310	-30		5	0,5 (0,05)
■ ECOPUR LD		-35			
■ G-ECOPUR		-30			
■ H-ECOPUR		+110			
■ S-ECOPUR		-20			
■ T-ECOPUR	1.4310	-50		10	0,2 (0,02)
■ SKF Ecoflas		-10	+200		
■ SKF Ecorubber-H		-25	+150		
■ SKF Ecorubber-1		-30	+100		
■ SKF Ecorubber-2		-20	+200		
■ SKF Ecorubber-3		-50	+150		
■ SKF Ecosil		-60	+200		

IMPORTANT NOTE: The stated operating conditions represent general indications. It is recommended not to use all maximum values simultaneously.

¹⁾ Surface speed limit values are valid only in the presence of a lubrication film.

²⁾ Depending on shaft diameter.

³⁾ Half speed value for greased applications.