


# X-ECOPUR H

*Thermoplastic polyurethane elastomer (TPU)  
raw material base polyester (hydrolysis resistant)*

DIN: YAU      ASTM: YAU

Property	Unit	Value	Standard
Standard color	–	Dark red	
Durometer hardness*	Shore A	97 ±1	DIN ISO 7619
Durometer hardness*	Shore D	60 ±3	DIN ISO 7619
Density	g/cm <sup>3</sup>	1,22 ±0,01	DIN EN ISO 1183-1
Tensile strength	MPa	≥ 45	DIN 53504
Elongation at break	%	≥ 350	DIN 53504
100% modulus	MPa	≥ 22	DIN 53504
Compression set:			
70 °C / 24 h, 20% compression	%	≤ 30	DIN ISO 815
100 °C / 24 h, 20% compression	%	≤ 35	DIN ISO 815
Tear strength	N/mm	160	DIN ISO 34-1
Abrasion	mm <sup>3</sup>	20	DIN ISO 4649
Minimum service temperature	°C	–20	–
Maximum service temperature	°C	+110	–

IMPORTANT NOTE: The values shown above are only valid for material samples prepared for test purposes according to the stated standards.

\* testing time is 3 s

© SKF and X-ECOPUR are registered trademarks of the SKF Group.

© SKF Group 2018

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

PUB SE/P8 12489/1 EN · July 2018

