

# Safety Data Sheet

## LGMT 2

Replaces date: 07/04/2025

Revision date: 05/08/2025

Version: 4.7.0

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Trade name: LGMT 2

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended uses: Lubricant.

Inadvisable uses: None.

#### 1.3. Details of the supplier of the safety data sheet

##### Supplier

Company: SKF UK Ltd  
Address: 400 Capability Green  
Zip code: LU1 3LU  
City: Luton  
Country: UNITED KINGDOM  
Email: technical.helpdesk.uk@skf.com  
Phone: +44 1582 490049  
Homepage: www.skf.com

#### 1.4. Emergency Telephone Number

Members of the public: 111 (NHS 111 (Scotland: NHS 24)).

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

CLP-classification: Skin Sens. 1;H317

Most serious harmful effects: May cause an allergic skin reaction.

# Safety Data Sheet

## LGMT 2

Replaces date: 07/04/2025

Revision date: 05/08/2025

Version: 4.7.0

### 2.2. Label elements

#### Pictograms



**Signal word:** Warning

#### Contains

**Substance:** Naphthenic acids, zinc salts, basic;

#### Hazard statements

H317 May cause an allergic skin reaction.

#### Precautionary statements

P280 Wear protective gloves.

### 2.3. Other hazards

The product does not contain any PBT or vPvB substances.

Endocrine disrupting properties: None known.

## SECTION 3: Composition/information on ingredients

### 3.2. Mixtures

Substance	CAS No./ EC No./ UK-REACH Reg. No.	Concentration	Notes	CLP-classification
Naphthenic acids, zinc salts, basic	84418-50-8 282-762-6	< 1.2 %		Skin Sens. 1;H317 Eye Irrit. 2;H319 Aquatic Chronic 3;H412  LD50 (Acute toxicity - dermal): > 2000 mg/kg bw LD50 (Acute toxicity - oral): > 2000 mg/kg bw
Benzenamine, N-phenyl-, reaction products with 2,4,4-trimethylpentene	68411-46-1 270-128-1	< 0.25 %		Repr. 2;H361f Aquatic Chronic 3;H412  LD50 (Acute toxicity - oral): > 5000 mg/kg bw LD50 (Acute toxicity - dermal): > 2000 mg/kg bw

Please see section 16 for the full text of H- / EUH-phrases.

**Ingredient comments:** The mineral oils in the product contain <3% DMSO extract(IP 346).

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

**Inhalation:** Seek fresh air. Seek medical advice in case of persistent discomfort.

**Ingestion:** Wash out mouth thoroughly and drink 1-2 glasses of water in small sips. Seek medical advice in case of discomfort.

**Skin contact:** Remove contaminated clothing. Wash skin with soap and water. Seek medical advice in case of persistent discomfort.

# Safety Data Sheet

## LGMT 2

Replaces date: 07/04/2025

Revision date: 05/08/2025

Version: 4.7.0

**Eye contact:** Flush with water (preferably using eye wash equipment) until irritation subsides. Seek medical advice if symptoms persist.

**General:** When obtaining medical advice, show the safety data sheet or label.

### 4.2. Most important symptoms and effects, both acute and delayed

May cause sensitisation by skin contact. Symptoms include reddening, swelling, blistering and ulceration - often slowly developing. The product contains at least one substance which is a suspected reproductive hazard.

### 4.3. Indication of any immediate medical attention and special treatment needed

Treat symptoms. No special immediate treatment required.

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

**Suitable extinguishing media:** Extinguish with powder, foam or water mist. Use water or water mist to cool non-ignited stock.

**Unsuitable extinguishing media:** Do not use water stream, as it may spread the fire.

### 5.2. Special hazards arising from the substance or mixture

Not flammable, but combustible. Product decomposes in fire conditions or when heated to high temperatures, and inflammable and toxic gases may be released.

### 5.3. Advice for firefighters

Wear Self-Contained Breathing Apparatus (SCBA) with chemical resistant gloves.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

**For non-emergency personnel:** Stay upwind/keep distance from source. Wear safety goggles if there is a risk of eye splash. Wear gloves.

**For emergency responders:** In addition to the above: Protective suit equivalent to EN 368, type 3, is recommended.

### 6.2. Environmental precautions

Prevent spillage from entering drains and/or surface water.

### 6.3. Methods and material for containment and cleaning up

Contain and absorb spill with sand or other absorbent material and transfer to suitable waste containers. Wipe up minor spills with a cloth.

### 6.4. Reference to other sections

See section 8 for type of protective equipment. See section 13 for instructions on disposal.

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Running water and eye wash equipment must be available. Wash hands before breaks, before using restroom facilities, and at the end of work.

# Safety Data Sheet

## LGMT 2

Replaces date: 07/04/2025

Revision date: 05/08/2025

Version: 4.7.0

### 7.2. Conditions for safe storage, including any incompatibilities

The product should be stored safely out of reach of children and not together with food, feed, medicine and the like. Keep in tightly closed original packaging. Do not store with the following: Strong oxidisers. Do not expose to heat (e.g. sunlight).

### 7.3. Specific end use(s)

None.

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

**Occupational exposure limit:** Contains no substances subject to reporting requirements.

**Measuring methods:** Compliance with occupational exposure limits may be checked by occupational hygiene measurements.

**Legal basis:** EH40/2005 Workplace exposure limits. Last amended January 2020. Control of Lead at Work Regulations 2002. Control of Asbestos Regulations 2012.

### 8.2. Exposure controls

**Appropriate engineering controls:** Wear the personal protective equipment specified below. Use the product under well-ventilated conditions.

**Personal protective equipment, eye/face protection:** Wear safety goggles if there is a risk of eye splash. Eye protection must conform to EN 16321.

**Personal protective equipment, hand protection:** Wear gloves. Type of material: Nitrile rubber. Breakthrough time has not been determined for the product. Change gloves often. Gloves must conform to EN 374. The suitability and durability of a glove is dependant on usage, e.g. frequency and duration of contact, glove material thickness, functionality and chemical resistance. Always seek advice from the glove supplier.

**Personal protective equipment, respiratory protection:** Not required.  
In case of risk of formation of spray mist, wear respiratory protective equipment with P2 filter. Respiratory protection must conform to one of the following standards: EN 136/140/145.

**Environmental exposure controls:** Ensure compliance with local regulations for emissions.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Parameter	Value/unit
State	Paste / Fat.
Colour	Red
Odour	No data
Solubility	Not miscible with the following: Water.

Parameter	Value/unit	Remarks
Odour threshold	No data	
Melting point	No data	
Freezing point	No data	

# Safety Data Sheet

## LGMT 2

Replaces date: 07/04/2025

Revision date: 05/08/2025

Version: 4.7.0

Boiling point or initial boiling point and boiling range	No data	
Flammability	No data	
Flammability limits	No data	
Lower and upper explosion limit	No data	
Flash Point	> 150 °C	
Auto-ignition temperature	No data	
Decomposition temperature	No data	
pH (solution for use)	No data	
pH (concentrate)	No data	
Kinematic viscosity	> 20.5 mm <sup>2</sup> /s	(40 °C)
Viscosity	No data	
Partition coefficient n-octanol/water (log value)	No data	
Vapour pressure	No data	
Density	< 1000 kg/m <sup>3</sup>	(25 °C)
relative density	No data	
Relative vapour density	No data	
Relative density (sat. air)	No data	
Particle characteristics	No data	

### 9.2. Other information

Parameter	Value/unit	Remarks
Explosive properties		Non-explosive

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

Reacts with the following: Strong oxidisers.

### 10.2. Chemical stability

The product is stable when used in accordance with the supplier's directions.

### 10.3. Possibility of hazardous reactions

None known.

### 10.4. Conditions to avoid

Avoid heating and contact with ignition sources.

### 10.5. Incompatible materials

Strong oxidisers.

### 10.6. Hazardous decomposition products

None, if stored at the recommended storage conditions.

## SECTION 11: Toxicological information

### 11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

#### Acute toxicity - oral

# Safety Data Sheet

## LGMT 2

Replaces date: 07/04/2025

Revision date: 05/08/2025

Version: 4.7.0

### LGMT 2

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
	ATE		4996.50 mg/kg		Calculated	

### Naphthenic acids, zinc salts, basic, cas-no 84418-50-8

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
Rat	LD50		> 2000 mg/kg bw			

### Benzenamine, N-phenyl-, reaction products with 2,4,4-trimethylpentene, cas-no 68411-46-1

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
Rat	LD50		> 5000 mg/kg bw			

The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met. Ingestion may cause discomfort.

### Acute toxicity - dermal

#### LGMT 2

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
	ATE		4689.60 mg/kg		Calculated	

### Naphthenic acids, zinc salts, basic, cas-no 84418-50-8

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
Rabbit	LD50		> 2000 mg/kg bw			

### Benzenamine, N-phenyl-, reaction products with 2,4,4-trimethylpentene, cas-no 68411-46-1

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
Rat	LD50		> 2000 mg/kg bw			

The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

### Acute toxicity - inhalation

### Naphthenic acids, zinc salts, basic, cas-no 84418-50-8

Organism	Test Type	Exposure time	Value	Conclusion	Test method	Source
Rat	LC50	4 h	> 420 mg/m <sup>3</sup>			

The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

#### Skin corrosion/irritation:

The product does not have to be classified. Test data are not available. May irritate the skin - may cause reddening.

#### Serious eye damage/eye irritation:

The product does not have to be classified. Test data are not available. Temporary irritation.

#### Respiratory sensitisation or skin sensitisation:

May cause sensitisation by skin contact. Symptoms include reddening, swelling, blistering and ulceration - often slowly developing.

#### Germ cell mutagenicity:

The product does not have to be classified. Test data are not available.

#### Carcinogenic properties:

The product does not have to be classified. Test data are not available.

#### Reproductive toxicity:

The product does not have to be classified. Test data are not available. The product contains at least one substance which is a suspected reproductive hazard.

#### Single STOT exposure:

The product does not have to be classified. Test data are not available.

#### Repeated STOT exposure:

The product does not have to be classified. Test data are not available.

# Safety Data Sheet

## LGMT 2

Replaces date: 07/04/2025

Revision date: 05/08/2025

Version: 4.7.0

**Aspiration hazard:** The product does not have to be classified. Test data are not available.

### 11.2. Information on other hazards

**Endocrine disrupting properties:** None known.

**Other toxicological effects:** None known.

## SECTION 12: Ecological information

### 12.1. Toxicity

**Benzenamine, N-phenyl-, reaction products with 2,4,4-trimethylpentene, cas-no 68411-46-1**

Organism	Species	Exposure time	Test Type	Value	Conclusion	Test method	Source
Fish	Danio rerio		96hLC50	> 100 mg/l			

The product contains small quantities of environmentally hazardous substances. The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

### 12.2. Persistence and degradability

Not expected to be biodegradable. Test data are not available.

### 12.3. Bioaccumulative potential

No bioaccumulation expected. Test data are not available.

### 12.4. Mobility in soil

Not expected to be mobile in soil. Test data are not available.

### 12.5. Results of PBT and vPvB assessment

The product does not contain any PBT or vPvB substances.

### 12.6. Endocrine disrupting properties

None known.

### 12.7. Other adverse effects

Oil products may cause soil and water pollution.

German water pollution classification (WGK): 1

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

Avoid discharge to drain or surface water. If this product as supplied becomes a waste, it does not meet the criteria of a hazardous waste (Dir. 2008/98/EU). Disposal should be in accordance with applicable regional, national and local laws and regulations. Local regulations may be more stringent than regional or national requirements. Empty, cleansed packaging should be disposed of for recycling. Uncleansed packaging is to be disposed of via the local waste-removal scheme.

**Category of waste:** EWC code: Depends on line of business and use, for instance 07 06 99 wastes not otherwise specified

Absorbent/cloth contaminated with the product: EWC code: 15 02 03 absorbents, filter

# Safety Data Sheet

## LGMT 2

Replaces date: 07/04/2025

Revision date: 05/08/2025

Version: 4.7.0

materials, wiping cloths and protective clothing other than those mentioned in 15 02 02

### SECTION 14: Transport information

**14.1. UN number or ID number:** Not applicable.

**14.4. Packing group:** Not applicable.

**14.2. UN proper shipping name:** Not applicable.

**14.5. Environmental hazards:** Not applicable.

**14.3. Transport hazard class(es):** Not applicable.

#### 14.6. Special precautions for user

None.

#### 14.7. Maritime transport in bulk according to IMO instruments

Not applicable.

**Other Information:** The product is not covered by the rules for transport of dangerous goods.

### SECTION 15: Regulatory information

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

**Special Provisions:** Special care should be applied for employees under the age of 18. Young people under the age of 18 may not carry out any work causing harmful exposure to this product.

Covered by:  
The Health and Safety (Young Persons) Regulations 1997.

#### 15.2. Chemical Safety Assessment

UK-REACH Reg. No.	Substance name
	Naphthenic acids, zinc salts, basic
	Benzenamine, N-phenyl-, reaction products with 2,4,4-trimethylpentene

### SECTION 16: Other information

#### Version history and indication of changes

Version	Revision date	Responsible	Changes
4.7.0	05/08/2025	SRU	1,8,16

**Abbreviations:**  
PBT: Persistent, Bioaccumulative and Toxic  
vPvB: Very Persistent and Very Bioaccumulative  
STOT: Specific Target Organ Toxicity

**Other Information:** This safety data sheet has been prepared for and applies to this product only. It is based on our current knowledge and the information that the supplier was able to provide about the product at the time of preparation. The safety data sheet complies with applicable law on preparation of safety data sheets in accordance with Regulation 1907/2006/EC "The Registration, Evaluation and Authorization of Chemicals" as amended by the stationary UK REACH etc. (EU Exit) as subsequently changed.



# Safety Data Sheet

## LGMT 2

Replaces date: 07/04/2025

Revision date: 05/08/2025

Version: 4.7.0

**Training advice:** A thorough knowledge of this safety data sheet should be a prerequisite condition.

**Classification method:** Calculation based on the hazards of the known components.

### Hazard statements

H317	May cause an allergic skin reaction.
H319	Causes serious eye irritation.
H361f	Suspected of damaging fertility.
H412	Harmful to aquatic life with long lasting effects.

**Country:** GB