Piston pump unit

Product series KFG

For fluid grease and grease For use in SKF MonoFlex and SKF ProFlex centralized lubrication systems







Features:

- Delivery rates: 0.8 to 15 cm³/min
- Fluids delivered: Fluid grease and grease
- Reservoir capacities: 2 to 20 kg
- Patented grease follower plate system for position-independent application (e.g. rotary application in wind energy systems)
- Integrated fill level monitoring
- Control unit that can be integrated
- For us in vehicles, Industrial and wind energy systems
- The commercial vehicle version has type approval pursuant to ECE-R 10

Advantages:

- Reliable: due to sturdy materials, very durable components and designs for extreme conditions (with positively driven pump elements)
- Application-oriented: individual designs through user-friendly product customizer
- Versatile: can be used as a single line (SKF MonoFlex) and as a progressive pump (SKF ProFlex)
- Safe: through fill level monitoring, lubrication system monitoring, pressure relief and control unit



Important information on product usage
SKF and Lincoln lubrication systems or their components are not approved for use with gases, liquefied gases, pressurized gases in solution and fluids with a vapor pressure exceeding normal atmospheric pressure (1 013 mbar) by more than 0,5 bar at their maximum permissible temperature.

Table of contents

| Product selection table | Product customizer |
|---|--|
| Introduction 4 | Dimensioned drawings |
| Fields of application | Technical data |
| Functional description in SKF centralized lubrication systems | Accessories |
| SKF Centralized tubrication systems | Special designs |
| Main components | Exploded-view and spare parts drawings |
| Designs10 | Wearing parts and spare parts |

Productselection table

| Overview | | SKF system fam | nily | Field of ap | plication | | Page |
|-------------------------------|---|----------------|-------------|-----------------------|-----------------------|-----------------------|---------------------------------|
| | | SKF MonoFlex | SKF ProFlex | Rotary | Industry | Vehicle | |
| Control unit | Without internal and external control unit Internal control unit IG502-2-I Internal control unit LC502 | - - • | • | • | : | • | 8 8 8 |
| Reservoir capacity [kg] | 2 4 6 8 10 12 15 20 | • | • | - • • • • | • • • • • | • - • - • | 7 7 7 7 7 7 7 |
| Pump element | With positively driven piston With spring-return piston | : | : | : | : | : | 6 |
| Fill level indicator | None With mechanical fill level switch With mechanical fill level switch and signal smoothing With capacitive proximity switch With cylinder switch | : | • | • - - - | • • • • | • • - | 7 7 7 7 |
| Metered quantity | 0.8–5 cm³/min (per outlet) | • | • | • | • | • | 6 |
| Filling | Lubricant nipple Socket for filling cylinder Filler coupling on reservoir cover | : | • | - - • | • • | • • | 6 9 7 |
| Valves | None Relief valve incl. pressure restriction valve Pressure restriction valve | - • - | • - | : | : | • | 9 9 9 |
| Elect. connection | 12 V DC 24 V DC 230 V AC (100–273 V AC) | : | : | <u>.</u> | • | • • | 6 6 6 |

Introduction

The KFG pump unit is an electrically driven piston pump. Its core is comprised of a drive shaft with an eccentric that drives up to three pump elements. Various designs make it possible to accommodate this sturdy and proven principle of operation to different circumstances.

The pump is comprised of four main components: Housing with pump elements, reservoir with fill level monitoring, internal control units and attachments. The housing integrates the motor, the drive shaft with an eccentric and up to three pump elements for delivering the lubricant. Positively driven pump elements should be used in order to maintain the delivery rate in areas with extremely low temperatures or in applications where an increased influence of dirt is unavoidable.

The reservoir is used for storage of the lubricant. It is available in eight sizes and two variants for stationary utilization or with grease follower plate technology for utilization in any position. The internal control units monitor the switching on and off of the pump. In addition, they enable the evaluation of piston detector, pressure switch and fill level signals. A variety of attachments permit the filling of the reservoir, protect the pump (pressure limitation valve), relieve the system (only when used in single-line systems) or enable the uncomplicated connection of the pump to the centralized lubrication system.



Fields of application



Vehicle

It is particularly with changing operating conditions that vehicles must function reliably. KFG piston pump units are the heart of SKF centralized lubrication systems for vehicles. They supply all of the connected lubrication points in an optimum manner and thus reduce service and repair costs but up to 25%.



Industry


Friction, e.g. in machine tools, causes great wear and thus wastes valuable natural resources. SKF centralized lubrication systems with KFG pump units reduce friction and thus considerably extend the service life of machine tools, for example.




Rotary application

Centralized lubrication systems such as SKF WindLub with the KFG pump unit for rotary application reduce the wear on modern wind energy systems and thus ensure a long preservation of value. They shorten the time required for repair and lengthen the repair intervals. That saves money.

Functional description in SKF centralized lubrication systems





SKF MonoFlex - Single-line centralized lubrication systems

The SKF MonoFlex System is comprised of:

- Pump unit with pump element(s) and relief valve
- Lubricant lines
- Single-line distributors
- Pressure switch for pump control unit and monitoring

When the pump motor is turned on, the pump element suctions the lubricant out of the reservoir and conveys it to through the relief valve to the lubrication line. Through this it flows to the single-line distributors. There it is metered and forwarded to the lubrication points during the pump runtime. Once the pressure build-up is completed, the relief valve, controlled by a pressure switch, switches over. As soon as the main line is relieved of pressure, the system is ready for the next lubrication cycle

SKF ProFlex - progressive centralized lubrication systems

The SKF ProFlex System is comprised of:

- Pump unit with pump component(s)
- Lubricant lines
- Progressive feeders
- Optional piston detectors for function monitoring

When the pump motor is turned on, the pump element suctions the lubricant out of the reservoir and conveys it to the lubrication line. Through this it flows to the progressive feeder. There is is divided up, depending on how much lubricant is required at the lubrication points to be supplied.

In progressive systems with master and secondary feeders, the lubricant is first delivered to the master feeder. The master feeder distributes the lubricant to the secondary feeders according to their individual volume requirements. From there, the lubricant flows to the lubrication points. Piston detectors can be connected to the function monitoring. The function monitoring of a lubrication system with the aid of a single piston detector is possible, thanks to the positively driven distribution of the lubricant typical for progressive systems.

Main components

Pump housing

The housing of the KFG pump unit is made of sturdy aluminum. Integrated within are the electric motor, the power supply unit (only with 230 V AC variant), the drive shaft with eccentric and one to three pump elements. The eccentric converts the rotational movement into a stroke movement of the pump element. The pump element pushes out lubricant during its forward movement and suctions in new lubricant from the lubricant reservoir during its retraction movement.

In the design for the vehicle and industry sector, the lubricant reservoir is filled through a conical head nipple on the pump housing. In addition, two different control units (IG502-2-I and LC502) can be integrated as optional equipment. Their displays are attached in a readily accessible manner to the front side of the pump housing. Basically speaking, the pump unit is available with three voltage keys: 12 V DC, 24 V DC and 230 V AC. KFG pump units with control unit, a 230 V power supply unit or with mechanical fill level switch have a deep bottom (foot). The overall dimensions are changed as a result.





Pump elements


Pump elements deliver the lubricant to the lubrication points or distributors through lubrication lines. Five pump elements for delivery rates of from 0.8 to 5.0 cm³/min are available for selection in two designs:

- with spring-return piston
- with positively driven piston In many application instances, the pump element with spring-return piston is the correct choice. The pump element with positively driven piston was developed for use in extremely cold environments (to -30 °C).

or for high-viscosity lubricants. Up to three pump elements can be installed in the KFG pump unit. The possible attachment positions are located on the left (1), at the front (2) and on the right (3) on the pump housing. The lubricant outlet on the pump element has an M14x1.5 female thread for connecting lubrication lines or valves. If no pump element is installed, then the outlet of the pump housing is sealed with a screw.







Note

If more than one pump element is installed in a KFG pump unit for an SKF MonoFlex system, then their outlets will be consolidated externally to form one main lubrication line. The total delivery rate is then derived from the sum of the respective delivery rates of the individual pump elements.

| Marking of the pump elements | | | | | | | |
|---|--|-------------------------------|--|--|--|--|--|
| Model | Spring- return | Positively driven | | | | | |
| Delivery rate* [cm ³ /min] | Number of the marking grooves on the head of the pump element | Labeling | | | | | |
| 0,8 1,3 1,8 2,5 5,0 | 4 3 2 1 0 | - J-3 H-2 G-1 L-0 | | | | | |

The specified quantities refer to grease of NLGI class 2 at 20 °C and a back pressure of 50 bar.

Main components

Reservoir

Two different reservoir types exist for the KFG pump unit: one for stationary and one for rotary application. A grease follower plate system patented by SVK is to be found in the lubricant reservoir of the units for rotary application. A spiral spring assembly is attached to the grease follower plate. This presses the follower plate onto the lubricant. As a result, the lubricant is always available at the pump element, independent of the position of the unit. The filling of this reservoir variant is carried out through a quickaction coupling on the reservoir cover in accordance with the "First In - First Out" principle. This avoids having old grease in the lubricant reservoir. The initial filling of the reservoir is made by SKF. In the reservoirs without grease follower plate technology, for industry and vehicle applications, the lubricant is worked by an agitator. This avoids air pockets and improves pumpability.

The filling of the variants without grease follower plate technology takes place through the housing, as is described on page 6. Reservoir capacities of from 2 to 20 kg are available for vehicles and industrial plants and reservoir capacities of from 4 to 15 kg for rotary applications.

Depending on the field of application, three variants exist for monitoring the fill level in the lubricant reservoir: capacitive proximity switches, mechanical fill level switches and cylinder switches.

Cylinder switches are suitable for the reservoir model with grease follower plate. The capacitive proximity switch is suitable for stationary application with grease and fluid grease of the NLGI classes 1, 0, 00, and 000. The mechanical fill level switch is to be used for the stationary application with grease of NLGI class 2.





Fill level monitoring through mechanical fill level switches

The mechanical fill level switches are mounted on the agitator. The grease resistance causes them to pivot downwards when the reservoir is filled and the agitators rotate. When the minimum fill level is reached, the pressure of the grease is reduced to the rocker switch.

It pivots back and thus interrupts the contact to the solenoid switch. The mechanical fill level switches are used only in stationary KFG units for fill level monitoring of the lubricating medium of NLGI class 2 grease. A version with signal smoothing is also available for the evaluation of the signal with external control units.



Fill level monitoring through capacitive proximity switches

Capacitive proximity switches are contact-free sensors that react with an electrical switching signal when a medium approaches.

They are used in KFG pump units for minimum fill level monitoring of the lubricating medium fluid grease and grease up to NLGI class 1.



Fill level monitoring using cylinder switches


In the case of cylinder switches, contactless solenoid switches are used. They measure the change of the magnetic field and convert this into a digital signal. In the case of the KFG pump, they are used solely in units that have a grease follower plate. When several cylinder switches are used various switching points such as Minimum, Maximum of Fill level pre-warnings can be monitored by the detection of the position of the grease follower plate.



Main components

Internal control unit IG502-2-I

The control unit IG502-2-I with control display can be integrated in the pump housing and controls the turning on and off of the KFG pump by means of interval times and pump runtimes. It enables the fill level monitoring of the lubricant reservoir and the evaluation of a piston detector signal (setting of the control unit when a signal is expected from the piston detector during the runtimes: COP=CS). It is suitable exclusively for the monitoring of SKF ProFlex systems.



COP: Cycle Off Pressure (main line pressure off)

PS: Pressure-Switch (pressure switch)

CS: Cycle-Switch (piston detector)



Internal control unit LC502

The control unit LC502 offers the same range of functions as the IG502-2-I. In addition, it enables the control of single-line systems (SKF MonoFlex) through the evaluation of a pressure switch signal (setting of the control unit, if a signal is expected from the pressure switch during the runtimes): COP=PS).

With the LC502, it is possible to monitor two piston detectors in progressive systems (SKF ProFlex) simultaneously. (Setting of the control unit, if a signal is expected from the piston detector during the runtimes: COP=CS.)



Pump runtimes and interval times

In the control device Pump run-and pause times can be preset from factory. To make this possible a corresponding code letter

from the following table has to be entered in the order code on page 11.

| Runtimes IG502-2-I/LO | Runtimes IG502-2-I/LC502 | | | | | | |
|--|--------------------------|--|--|--|--|--|--|
| Pump runtime * [min] | Letter | | | | | | |
| 2 | A | | | | | | |
| 2,5 | В | | | | | | |
| 3 3 5 | C D | | | | | | |
| 4 | E F | | | | | | |
| 4,5 | | | | | | | |
| 2 2,5 3 3,5 4 4,5 5 5,5 | G H | | | | | | |
| 5,5 6 | Ï | | | | | | |
| 6,5 7 | J | | | | | | |
| 7 | K | | | | | | |
| 7,5 8 | L M | | | | | | |
| 8 8,5 | N | | | | | | |
| 9 | 0 | | | | | | |
| 9,5 10 | P Q | | | | | | |
| 11 | R | | | | | | |
| 12 | S | | | | | | |
| 13 | T U | | | | | | |
| 14 15 | V | | | | | | |
| 16 | W | | | | | | |
| 17 | X | | | | | | |
| 18 20 | Y Z | | | | | | |
| * further pump runtimes on requi | | | | | | | |

| Interv | al times IG502 | -2-I/LC502 |
|---|---|---|
| Pump pause time * | | ontrol Letter for control t unit with monitoring |
| 0,5 1 1,5 2 2,5 3 3,5 4 5 6 7 8 9 | A B C D E F G H I J K L M | N O P Q R S T U V W X Y Z |

* further pump pause times on request

Note

If during the pump runtime neither a pressure switch nor a piston detector signal is expected, then the control unit should be set as follows:

If a pressure switch signal is expected, then the control unit should be set as follows: COP=PS.

If a piston detector signal is expected, then the control unit should be set as follows: COP=CS.


PUB LS/P2 12649 EN · 1-3030-EN

Main components

Pressure restriction valve

In order to prevent an excessive operating pressure in the system, a pivoted pressure restriction valve should be attached. If the operating pressure exceeds the cracking pressure of the pressure restriction valve, then the valve will open and the lubricant can escape. The pressure restriction valve is used primarily in progressive systems. One can select among variants with SKF plug connectors, straight connector and with G 1/4" female thread.






Pressure relief valve with integrated pressure restriction valve

The valve offers both a pressure regulating and a pressure relief function. SKF MonoFlex systems require pressure relief for the system in order to conclude the metering of the distributors and thus to enable a new lubrication cycle. The pressure regulating function protects the system against excessive operating pressure. This valve is therefore used exclusively in single-line systems. One can select among variants with SKF plug connectors, straight connector and adapter for G 1/4" female thread.






Socket for filling cylinder

For industry and vehicle applications, one of the three lubricant outlets of the pump can, as an option, be equipped with one suitable filler socket instead of with one pump element, in order to fill the unit using a filling cylinder (cartridge).






Fittings

A variety of different fittings


with the male thread M14 \times 1.5 are available for selection for the connection of the pump element to the lubrication lines of the centralized lubrication system. One can select among cross sections 6, 8, 10 and 12 mm in size.

If a G 1/4" connection is required, then a special adapter must be used. Additional information regarding fittings and accessories are to be found in the leaflet **1-0103-EN**.









Designs











Fitting Cutting-sleeve screw union with sealing ring



Pressure restriction valve for progressive systems (SKF ProFlex)



KFG unit for Industry/Vehicle applications



KFG with grease follower plate technology for rotary application



Note This page shows possible designs of the KFG units.

Not all components can be combined with one another. The configurator on the following page allows the functional specification of a KFG reservoir pump unit.

Fill level monitoring

(mechan. switch for grease, NLGI class 2)



Fill level monitoring

(capacitive proximity switch for fluid grease,



Fill level monitoring

(cylinder switch for rotary application)



Pump element (spring-return)



Pump element (positively driven)




Order example

KFGS3FXXAXXDEB+924

- KFG piston pump unit
- IG502-2-I Control Unit
- Reservoir capacity 6 kg Vehicle application
- Without lubricant filling
- Without fill level monitoring
- 2,5 cm³/min delivery rate of the pump element with spring-return pistons at outlet 1
- 8 mm fitting at the outlet
- Factory setting of the control unit System voltage 24 V DC

Product customizer





| Contr | rol unit Design | System family open | SKF ProFlex | SKF MonoFlex |
|-------|---------------------------|--------------------|-------------|--------------|
| Α | None control unit | X | X | X |
| | IG502-2-I | 5 | S | _ |
| | LC 502 | - | L | L |

| Pum | p element / Filler socket Design | Spring-return piston | Positively driven piston |
|-----|--|---------------------------------|----------------------------|
| F | without pump element 0,8 cm³/min 1,3 cm³/min 1,8 cm³/min 2,5 cm³/min 5,0 cm³/min socket for filling cylinder (not for rotary application) | X D C B A E W | Y - J H G L |

| Pump cycle time/Interval time | | | | | | |
|---|-----------------------------|------|------------------|--|--|--|
| | Control unit | none | IG502-2-I/LC502 | | | |
| Н | Runtime ¹⁾ | 9 | E (4 min) | | | |
| J | Interval time ¹⁾ | 9 | B (1 h) | | | |
| 1) Factory setting, additional setting times → Tables on page 8 | | | | | | |

| December of the field of application lubricant filling |
|---|
| Reservoir capacity, field of application, lubricant filling |
| |
| fill level monitoring and voltage key |

| | Range of application | Rotary | Industry | Vehicle |
|---|---|---------------------------------|--------------------------------------|--------------------------------------|
| С | | R | М | F |
| В | 2 kg 4 kg 6 kg 8 kg 10 kg 12 kg 15 kg 20 kg | - 2 3 4 5 6 7 | 1 - 3 - 5 - 7 8 | 1 - 3 - 5 - 7 8 |
| D | without lubricant grease NLGI-Klasse 2 ²⁾ customized grease | – A F | X A F | X A F |
| Е | without fill level monitoring mechanically (minimum) mechanically with signal smoothing (minimum) ³⁾ capacitive (minimum) cylinder switch | X - - - 4 | X 1 2 3 4) | X 1 2 - |
| K | 12 V DC 24 V DC 230 V AC (100–273 V AC) | - 924 486 | - 924 486 | 912 924 - |

- Typical grease for vehicle lubrication, not for capacitive fill level monitoring (3)
 Possible only with the variant without control unit (KFGX)
 Possible only in combination the reservoir capacities 2 kg and 6 kg

Fitting, pressure restriction valve (PRV) and relief valve 5) for attachment to the pump element


| | Systemfamily | SKF ProFlex | SKF ProFlex | SKF ProFlex | SKF ProFlex | SKF ProFlex | SKF ProFlex | SKF MonoFlex 6) | SKF MonoFlex 6) |
|---|--|-----------------------------|------------------|---|---|---|---|--|--|
| | Design | Without attach- ments | | PRV 200 bar with straight connector | PRV 200 bar with SKF plug connector | PRV 300 bar with straight connector ⁷⁾ | PRV 300 bar with SKF plug connector ⁷⁾ | Pressure relief valve with PLV 200 bar and straight connector | Pressure relief valve with PRV 200 bar and SKF plug connector |
| G | M14×1,5 ⁸⁾ G ¹ /4" ⁸⁾ 6 mm 8 mm 10 mm 12 mm | X B - - | - C D E | - - - M N | - - - P - | - G Н Ј К | - F L | - W - V U | - - S T - |


- 5) For technical reasons, the first pump element must always be installed at Outlet 1 in SKF MonoFlex systems.
 6) If the relief valve is configured together with several pump elements, then the lines leading from the pump elements will be joined together ahead of the relief valve.
 7) Not possible in combination with the pump elements E and L
 8) Female thread

SKF

Dimensioned drawings

Important note Starting with a reservoir filling capacity of 10 kg, the only fastening permitted is with the retaining ring on the reservoir.







PUB LS/P2 12649 EN · 1-3030-EN

Dimensioned drawings

Important note Starting with a reservoir filling capacity of 10 kg, the only fastening permitted is with the retaining ring on the reservoir.





Technical data

| General information | |
|--|--|
| Operating temperature: spring-return pump elements (for 115/230 V AC only to +60 °C) | -25 to +70 °C |
| Positively driven pump elements (for 115/230 V AC only to +60 °C) | -30 to +70 °C |
| Lubricant | NLGI Grades 000 to 2 with EP additives, compatible with plastics, NBR elastomers, copper and copper alloys |
| Flow pressure | up to max. 700 mbar |
| Flow pressure(Pump elements with 5.0 cm ³ /min) | up to max. 450 mbar |

| Weight empty of the | pump without attachments |
|---------------------|--------------------------|
|---------------------|--------------------------|

to DIN 40050, T9 IP56

| Rotary app Reservoir capacity | | Stationary a Reservoir capacity | |
|---|--|---|---|
| 4 kg 6 kg 8 kg 10 kg 12 kg 15 kg | 11 kg 12 kg 14 kg 15 kg 17 kg 18 kg | 2 kg 6 kg 10 kg 15 kg 20 kg | 6 kg 7 kg 14 kg 16 kg 18 kg |

Pump housing and reservoir

Protection class according

Pump housing material Aluminum-silicon cast alloy

Reservoir material:

. Polyamide PA 61 2, 6 kg 4, 8, 10, 12, 15, 20 kg PMMA

System voltage 12 V DC, 24 V DC, 230 V AC (90–264 V AC)

Connector plug Variant - 7-pin circular plug

- 12-pin elbow connector M16x0.75 - 4-pin circular plug/socket M12x1

(IEC 60947-5-2 cable socket)

- 4-pin square connector (DIN EN 175301-803 cable socket)

Operating mode/ON-time according to EC 60034-1, DIN EN 60034-1 and VDE 0530-1

12/24 V DC S1 (continuous duty, constant loading)

90 to 264 AC

(25 °C to 40 °C) S1 (continuous duty, constant loading)

Operating modes or on/pause times for different temperature ranges, please see operating instructions

General conditions for electrical connections

| Rated voltage | Power con-sump-tion 1) | Power con-sumption (max) | Pump starting current (approx. 20 ms) | Maximum back-up fuse for industrial and rotary application | Maximum back-up fuse for ve- hicle appli- cation ²⁾ |
|--|------------------------|------------------------------------|---|--|--|
| 12 V DC 24 V DC 115 V AC 230 V AC | 1.25 A K.A. | < 5 A < 2.5 A 1.8 A 0.9 A | 9 A 4.5 A < 20 A < 30 A | – 4 AT C6A ³⁾ C6A ³⁾ | 5 AT 3 AT – |

- Typical values for an ambient temperature of approx. 25 °C and an operating pressure of 150 bar (load-dependent)
 Fuse protection in accordance with DIN72581T3
 Fuse protection of the characteristic C

Pump elements

| _ | | | | | | | |
|---|----|-----|---|----|-----|----|---|
| ח | ام | iv. | ۵ | r١ | ı r | ٦t | ۵ |

Spring-return pump element 0.8; 1.3; 1.8; 2.5; 5.0 cm³/min

Positively driven pump element 1.3; 1.8; 2.5; 5.0 cm³/min

Maximum back pressure:

Spring-return pump element 300 bar (200 bar for pump element with 5.0 cm³/min)

Positively driven pump element 350 bar (250 bar for pump

element with 5.0 cm³/min)

Mechan. fill

Fill level switch

| | Capacitive proximity switches | Mechan- ical fill level switch | level switch with signal smoothing | Cylinder switch |
|-------------------------|-------------------------------|--------------------------------------|--|--------------------|
| Max. switched voltage | 10-30 V DC | 24 V DC | 30 V DC | 1-48 V AC/DC |
| Max. switched current | 200 mA | 25 mA | n.s. | 0.5 A |
| Max. switching capacity | n.s. | 0.6 W | 60 W | 5 W |
| Type of contact | NO-contact | NO-contact | Changeover | Changeover |

Connection:

for KFG without 4-pin circular 4-pin circular 4-pin circular Square plug M12x1 plug M12x1 socket M12x1connector ⁴⁾ (Industry) (Industry) control unit

> 7-pin circular 7-pin circular plug (Vehicle) plug (Vehicle)

| for KFG with control unit | | | - | Internal connection 5) |
|----------------------------|---------|---|---|------------------------|
| Internal power consumption | 6–12 mA | - | - | - |

Voltage drop ≤ 1.8 V

4) Cable socket according to DIN EN 175301-803 5) Only for use with the IG502-2-I or the LC502 230 V; when using the LC502 24 V, the connection is a 4-pin circular connector M12x1

Accessories

Filler coupling


As an alternative to a conical head nipple, the units for industrial or vehicle applications can also be equipped with a filler socket in order to fill it with a filling pump, e.g. the manual drum pump. A corresponding coupling socket and a hose socket must be mounted on the filling pump.



Filling coupling Part A

Description Order number

Filler socket with sealing ring 24-9909-0244






Filler coupling Part B

Description Order number

Coupling socket 995-001-500





Filler coupling Part C

Description Order number

Hose socket:

857-760-007 ø13 mm ø16 mm 857-870-002

Filling cylinder

For industry and vehicle applications, a filling cylinder can also be optionally used to fill the pump unit through one of the lubricant outlets. To accomplish this, a filler socket must be configured in the order code in place of a lubricant outlet.



Filling cylinder

Description

Order number

Filling cylinder (socket for filling cylinder w must be configurated on KFG pump in the order code on page 11)

169-000-171

Manual drum pump

The manual drum pump is for simple fillingup of the KFG piston pump unit. It is available in the designs with and without trolley and is suitable for NLGI class 1 and 2 greases. The delivery rate of the drum pump is approx. 40 cm³/stroke.



Drum pump

Description Order number

Drum pump with running gear:

For 25 kg drum

169-000-042 169-000-054 For 50 kg drum

Drum pump without running gear:

For 25 kg drum 169-000-342

PUB LS/P2 12649 EN · 1-3030-EN

SKF

Accessories

IG502-2-E external control unit

The IG502-2-E is an external control unit with a control display. It controls the turning on and off of the KFG pump by means of interval and pump runtimes. Furthermore, it enables the fill level monitoring of the lubricant reservoir and the evaluation on one piston detector signal. In addition, one can operate the pump unit with it, even from a short distance, e.g. from the cab of a vehicle. It is suitable only for SKF ProFlex systems.



| External control | l unit |
|-----------------------|---|
| Description | Order number |
| External control unit | IG502-2-E+912 (control voltage 12 V) |
| | IG502-2-E+924 (control voltage 24 V) |
| | |
| | |
| | |

Retaining ring and drilling template

For all KFG units with reservoir capacities up to and including 6 kg, a special drilling template exists as an installation aid made of self-adhesive foil. In addition to that, a stabilizing retaining angle is also available for vertical installation.



| netaning ing ana and | my temptate |
|---------------------------------|--------------|
| Description | Order number |
| Self-adhesive drilling template | 951-130-115 |

881-290-430

Retaining ring and drilling template

Electrical accessories

The T plug is suitable when additional connectors are required, e.g. for a separate indicator lamp.



Electrical accessories

Pump retaining plate

Description Order number

T-plug M12×1 with two outgoing cables (socket M12×1)

Together number

179-990-700

Pressure gauge

Reed pen pressure gauges with glycerin filling are available for visual documentation of the pressures in the SKF centralized lubrication system. The parts which come into contact with the medium are made of copper alloys. These pressure gauges are suitable for highly dynamic pressure loads and vibrations. The necessary accessory parts for fastening are to be found in the leaflet 1-0103-EN.



| Pressure gauge | |
|---|--|
| Description | Order number |
| Pressure gauge, complete: 0 to 250 bar 0 to 400 bar | 169-125-000.U1 169-140-001.U1 |
| Pressure gauge screw union: for ø 6 mm tubing for ø 8 mm tubing for ø 10 mm tubing for ø 12 mm tubing | 471-106-163 471-108-163 471-110-163 471-112-163 |

PUB LS/P2 12649 EN · 1-3030-EN

16

Special designs

KFG with CAN bus control unit (KFGC)

The KFGC (CAN bus) variant is based on the KFG series and has an integrated CAN bus control unit (LC-CAN5000). The control unit with the CAN bus interface SAE J1939 permits the integration of the lubrication system in the CAN bus and thus enables the input and evaluation of a large number of parameters for the control unit and monitoring of the system. It can however also be used as a stand-alone solution and be connected to a PC via a CAN bus plug/CAN bus adapter or through an infrared interface.

Interesting for:

- all those who use CAN bus and who would like to enter, display and evaluate the lubrication system data at a central location
- all those who require individual settings and monitoring of up to four independent valves and/or lubrication circuits (complex systems)
- all those who wish to call up the error log through the PC

Result:

Implementation of tailored lubrication concepts for each lubrication circuit in the lubrication system (independent and according to need).







Note

For inquiries regarding possible variants and designs, please contact an SKF Lubrication Systems representative.

KFG sea water-resistant

Basically, all KFG variants are available in sea water-resistant versions. Individual components for protection against corrosion (corrosion class C5-M) are coated for this purpose and combined with stainless steel components.







Note

For inquiries regarding possible variants and designs, please contact an SKF Lubrication Systems representative.

Exploded-view and spare parts drawings





Only original spare parts from SKF Lubrication Systems
Germany GmbH may be used.
Unauthorized alterations to products

Unauthorized alterations to products and the use of non-original spare parts and accessories are not permitted.

Dismantling of the product or individual parts thereof within the statutory warranty period is not permitted and voids any claims.

Repair work may only be performed by the Service department of SKF Lubrication Systems Germany GmbH. In the event of questions in reference to installation or maintenance, please contact SKF Lubrication Systems Germany GmbH or a an SKF-authorized dealer or service partner.







| Wearing parts | | | | | | | |
|---------------|--------------|-------------------------|---|--|--|--|--|
| Pos. | Order number | ID used in configurator | Description | | | | |
| 1 | KFG1.U0 | E | Pump element with spring-return piston 5,0 cm ³ /min | | | | |
| 2 | KFG1.U1 | Α | Pump element with spring-return piston 2,5 cm ³ /min | | | | |
| 3 | KFG1.U2 | В | Pump element with spring-return piston 1,8 cm ³ /min | | | | |
| 4 | KFG1.U3 | C | Pump element with spring-return piston 1,3 cm ³ /min | | | | |
| 5 | KFG1.U4 | D | Pump element with spring-return piston 0,8 cm ³ /min | | | | |
| 6 | KFG1.U0-E | L | Pump element with positively driven piston 5,0 cm ³ /min | | | | |
| 7 | KFG1.U1-E | G | Pump element with positively driven piston 2,5 cm ³ /min | | | | |
| 8 | KFG1.U2-E | Ĥ | Pump element with positively driven piston 1,8 cm ³ /min | | | | |
| 9 | KFG1.U3-E | J | Pump element with positively driven piston 1,3 cm ³ /min | | | | |

Spare parts

| s. | Order number | ID used in configurator | Description |
|----------|-----------------------------------|-------------------------|---|
| 0 | 301-034 | В | Adapter M14x1.5 on G1/4 (sealing ring Item 11 must be ordered separately) |
| 1 | DIN7603-A14X18-AL | | Washer |
| .2 | 406-413 | С | Straight connector for tube ø 6 mm GE 6-L M14x1,5 |
| .3 | 408-413 | D E | Straight connector for tube ø 8 mm GE 8-S M14x1,5 |
| .4 .5 | 410-403 161-210-063 | M | Straight connector for tube ø 10 mm GE 10-L M14x1,5 PRV ¹⁾ 200 bar, straight connector ø 8 mm |
| .6 | 161-210-065 | N | PRV ¹) 200 bar, straight connector ø 10 mm |
| .7 | 161-210-062 | Ö | PRV 1) 200 bar, straight connector ø 12 mm |
| L8 | 161-210-061 | Р | PRV ¹⁾ 200 bar, SKF plug connector ø 8 mm |
| 19 | 161-210-036 | G | PRV ¹⁾ 300 bar, female thread G1/4 |
| 20 | 161-210-012 | H | PRV 1) 300 bar, straight connector ø 6 mm |
| 21 22 | 161-210-024 161-210-066 | J K | PRV $^{1)}$ 300 bar, straight connector ø 8 mm PRV $^{1)}$ 300 bar, straight connector ø 10 mm |
| 23 | 161-210-000 | F | PRV ¹ 300 bar, SKF plug connector ø 6 mm |
| 24 | 161-210-034 | Ĺ | PRV 1) 300 bar, SKF plug connector ø 8 mm |
| 25 | 24-1254-2634 | W | Relief valve with PRV 1) 200 bar, female thread G1/4, 12 V design |
| 26 | 24-1254-2635 | W | Relief valve with PRV ¹⁾ 200 bar, female thread G1/4, 24 V design |
| 27 | 24-1254-2636 | W | Relief valve with PRV ¹⁾ 200 bar, female thread G1/4, 230 V design |
| 28 29 | 24-1254-2640 | V | Relief valve with PRV 1) 200 bar, straight connector ø 8 mm, 12 V design |
| 29 30 | 24-1254-2641 24-1254-2642 | V | Relief valve with PRV ¹⁾ 200 bar, straight connector ø 8 mm, 24 V design Relief valve with PRV ¹⁾ 200 bar, straight connector ø 8 mm, 230 V design |
| 31 | 24-1254-2637 | Ŭ | Relief valve with PRV ¹⁾ 200 bar, straight connector ø 10 mm, 12 V design |
| 32 | 24-1254-2638 | Ŭ | Relief valve with PRV ¹⁾ 200 bar, straight connector ø 10 mm, 24 V design |
| 33 | 24-1254-2639 | U | Relief valve with PRV 1) 200 bar, straight connector ø 10 mm, 230 V design |
| 34 | 24-1254-2643 | S | Relief valve with PRV ¹⁾ 200 bar, SKF plug connector ø 6 mm, 12 V design |
| 35 | 24-1254-2644 | S | Relief valve with PRV ¹⁾ 200 bar, SKF plug connector ø 6 mm, 24 V design |
| 36 | 24-1254-2645 | S | Relief valve with PRV 1) 200 bar, SKF plug connector ø 6 mm, 230 V design |
| 37 38 | 24-1254-2646 24-1254-2647 | T | Relief valve with PRV 1) 200 bar, SKF plug connector ø 8 mm, 12 V design Relief valve with PRV 1) 200 bar, SKF plug connector ø 8 mm, 24 V design |
| 39 | 24-1254-2648 | Ť | Relief valve with PRV ¹ 200 bar, SKF plug connector ø 8 mm, 230 V design |
| 40 | KFGS1.54 | _ | Transparent cover for the control unit |
| 41 | 24-9909-0241 | _ | KFG filling nipple G1/4 kit |
| 42 | 24-9909-0248 | _ | KFG PRV 1) in the housing 1.5 bar G1/4 kit (rotary application) |
| 44 | 24-9909-0247 | - | KFG PRV in the housing 1.5 bar M20x1.5 kit (rotary application) |
| 45 | 169-000-174 | _ | KFG filler socket M20x1.5 kit (Industry, Vehicle) |
| 46 48 | KFG1.128 24-9909-0244 | _ | Screw plug, plastic, with 0-ring M20x1.5 (Industry, Vehicle) KFG filler coupling G1/4 kit |
| 49 | 24-9909-0249 | _ | KFG PRV ¹⁾ on the housing cover 30 bar G1/4 kit (rotary application) |
| 50 | 24-9909-0243 | _ | KFG fastening kit (for reservoir capacities from 8 kg to 20 kg only) |
| 51 | 24-9909-0246 | _ | KFG sensor/actuator box kit, 230 V (+486) Industry or rotary application |
| 52 | 24-9909-0254 | - | KFG fill level monitoring with square connector kit (rotary application) |
| 53 | 24-9909-0252 | - | KFG fill level monitoring with M12x1 plug (rotary application) |
| 54 55 | 408-313 | _ | Threaded socket XGE 8-LM M14x1,5 |
| 56 | 443-308-351 44-1751-2953 | _ | Elbow connector Pre-bent pipe 8x1 L-bend left |
| 57 | 44-1751-2954 | _ | Pre-bent pipe 8x1 L-bend right |
| 58 | 445-808-351 | _ | T-screw connection M14x1.5 tube Ø8mm |
| 59 | 44-1751-2956 | - | Pre-bent pipe 8x1 U-bend |
| 60 | 44-1751-2955 | - | Pre-bent pipe 8x1 L-bend |
| 61 62 | 24-9909-0245 DIN7603-A16X20-AL | <u>-</u> | SKF MonoFlex return line G1/4 kit Washer |
| 52 53 | 995-800-138 | 1 | vasner 2 kg reservoir with lid without level monitoring (industry and vehicle application) |
| 63 | 995-800-508 | 1 | 2 kg reservoir with lid with mechanically level monitoring (industry and vehicle application) |
| 63 | 995-800-501 | 1 | 2 kg reservoir without lid (industry, vehicle application) |
| 63 | 995-800-503 | 1 | Lid for 2 kg reservoir 995-800-501, for capacitive level monitoring (industry) |
| 63 | 995-800-500 | 3 | 6 kg reservoir without lid and without level monitoring (industry and vehicle application) |
| 63 42 | 995-800-504 | 3 | Lid for 6 kg reservoir 995-800-500 without level monitoring (industry and vehicle application) |
| 63 63 | 995-800-509 995-800-505 | 3 | 6 kg reservoir without lid with mechanically level monitoring (industry and vehicle application) Lid for 6 kg reservoir 995-800-500, for capacitive level monitoring (industry) |
| 53 53 | 24-0254-2791 | 5 | 10 kg reservoir without or with mechanically level monitoring (industry) |
| 63 | 24-0254-2771 | 7 | 15 kg reservoir without or with mechanically level monitoring (industry and vehicle application) |
| 63 | 24-0254-2789 | 8 | 20 kg reservoir without or with mechanically level monitoring (industry and vehicle application) |
| 63 | 177-300-113 | 3 | Capacitive level sensor for 2 kg reservoir 995-800-501 (industry) |
| 63 | 177-300-114 | 3 | Capacitive level sensor for 6 kg reservoir 995-800-500 (industry) |





CAD models for products shown in this brochure can be downloaded at: skf-lubrication.partcommunity.com

Further leaflets:

| 1-0103-EN | Fittings and accessories |
|-----------|---|
| 1-9201-EN | Feeding lubricants with centralized lubrication systems |
| 1-1701-EN | Pressure switches, product series DSA, DSB, DSC, DSD |
| 1-3010-EN | Modular feeder PSG (Progressive feeder) |
| 1-3015-EN | Sectional feeder VPK (Progressive feeder) |
| 1-3016-EN | Sectional feeder VP (Progressive feeder) |
| 1-3017-EN | Sectional feeder VPB (Progressive feeder) |
| 1-5001-FN | Luhricant distributor SKF MonoFlex (single-line distributor |

SKF Lubrication Systems Germany GmbH

Walldorf Plant Heinrich-Hertz-Str. 2-8 69190 Walldorf Germany

Tel. +49(0)6227-33-0 Fax +49(0)6227-33-259

E-Mail: lubrication-germany@skf.com

| Thic | loaflat | wac | nrocon | +04+ | hw |
|------|---------|-----|--------|------|--------|

 $@ \mathsf{SKF}, \mathsf{SKF} \ \mathsf{MONOFLEX}, \mathsf{SKF} \ \mathsf{PROFLEX} \ \mathsf{and} \ \mathsf{SKF} \ \mathsf{WINDLUB} \ \mathsf{are} \ \mathsf{registered} \ \mathsf{trademarks} \ \mathsf{of} \ \mathsf{the} \ \mathsf{SKF} \ \mathsf{Group}. \\$

© SKF Group 2023

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential, arising out of use of the information contained herein.

PUB LS/P2 12649 EN · January 2023 · 1-3030-EN

This publication replaces publications 1-3034-EN and 1-3035-EN.

